

Desk Mount Dual Monitor Arm – Premium Articulating Multi-Monitor Desktop VESA Mount up to 27" Displays – Adjustable Height/Rotating/Swivel/Tilt - Desk Clamp/Grommet - Silver

Product ID: ARMDUALPS



Create an ergonomic workspace with this premium desk-mount dual monitor arm, for monitors up to 27" each. The two articulating monitor arms with dual-swivel action offer a wide range of motion side to side. The attractive silver finish enhances the aesthetics of your workspace.



Enjoy a Wide Range of Motion to Work in Comfort

The dual articulating monitor arms offer a wide range of motion on several axes. It provides effortless motion to adjust the position of your monitors.



Sleek and Stable Aluminum Design

The robust aluminum design provides stable support for your monitors. The computer-monitor desk mount supports two VESA mount monitors (75x75, 100x100) with a weight capacity of up to 22 lb. (10 kg) per display. The cable-management channel helps to keep your workstation neat and tidy.

Adjust your Viewing Angle

Share your screen with ease. The double monitor mount offers a full +180-degree / -180-degree pan, to move your screen left or right. It tilts freely +90 / -15 degrees to adjust the angle up or down. Rotate your screens for landscape or portrait viewing.

Height Adjustment

Work in comfort. This height-adjustable monitor mount lets you raise or lower the monitor arms along the pole, with a range of up to 6.3" (160 mm)

Tool-less Assembly

The fully assembled desk clamp and pole, plus quick slide-and-click connections, ensure easy assembly. It also saves time when setting up multiple units. The dual-screen mount gives you the option of desk clamp or grommet hole mounting (hardware included).

The TAA compliant ARMDUALPS is backed by a StarTech.com 10-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Mount dual displays to the side of your desk or table in commercial, industrial or office settings
- Grommet mount your displays for dual-screen access in a media room
- Spread displays apart or position them back to back for multi-user workstations
- Rotate displays to portrait orientation for web design and coding

Features

- **HEAVY DUTY MONITOR MOUNT:** VESA 75x75/100x100mm compatible dual monitor arm supports two large displays up to 27" (22lbs) per screen; Horizontal articulating & height adjustable desk/grommet hole clamp
- **EASY INSTALLATION:** Premium dual monitor arm w/ convenient toolless slide & click design makes assembling the monitor arms & VESA adapters easy, reducing set-up time; Pre-assembled desk clamp & pole
- **WIDE RANGE OF MOTION:** Ergonomic monitor mount w/ +90°/-15° tilt, +/-180° swivel, 360° portrait/landscape rotating, adjustable height along 6.3" (16cm) pole & arms rotate for back-to-back monitor setup
- **ORGANIZED WORKSPACE:** Desktop double monitor mount w/ cable management clips along the silver arms & center pole to organize cables & hold incl. articulation tension adjustment tool for a tidy setup
- **APPLE DISPLAY COMPATIBILITY:** Snap & click accessory for StarTech.com premium mounts (APLVESAMNTP sold separately) lets you mount non-VESA monitors incl iMac/iMac Pro/Apple Cinema/Thunderbolt displays

| | | |
|---------------------------------|-------------------------------|--|
| Hardware | Warranty | 10 Years |
| | # of Displays Supported | 2 |
| | Articulating | Yes |
| | Cable Management | Yes |
| | Mounting Options | Desk & Grommet Clamp |
| | Mounting Surface Thickness | Desk Clamp: Table Thickness 0.78 - 2.36 in. (20 - 60 mm) Grommet Clamp: Table Thickness 0.78 - 2.36 in. (20 - 60 mm) Grommet Mount Hole Size: 0.39 - 2.36 in. (10 - 60 mm) |
| Performance | VESA Hole Pattern(s) | 75x75 mm 100x100 mm |
| | Display Rotation | 360° |
| | Display Swivel | +180° / -180° |
| | Display Tilt | +90° / -15° |
| | Maximum Arm Extension | 16.5 in [420 mm] |
| | Maximum Arm Span | 37 in [940 mm] |
| | Maximum Display Size | 27in |
| | Minimum Display Size | 13" |
| Physical Characteristics | Weight Capacity (Per Display) | 22.1 lb [10 kg] |
| | Color | Silver |
| | Material | Aluminum |
| | Product Height | 20.5 in [520 mm] |
| | Product Length | 8.7 in [220 mm] |
| | Product Width | 7.5 in [190 mm] |
| Packaging Information | Weight of Product | 158.2 oz [4482 g] |
| | Package Height | 18.3 in [465 mm] |
| | Package Length | 12.6 in [320 mm] |
| | Package Width | 5.7 in [145 mm] |
| What's in the Box | Shipping (Package) Weight | 194.1 oz [5500 g] |
| | Included in Package | 4 - Swivel Arms 2 - VESA Monitor Mounts 1 - Shoulder |

- 1 - Desk Clamp and Pole Assembly
- 2 - M3 Hex Keys
- 1 - EVA Cushion
- 8 - Thumbscrews
- 1 - Cable-Management Clip
- 1 - User Manual

Product appearance and specifications are subject to change without notice.