



# 2MP Bullet IP Camera with Junction Box

## O2B6M

2.9-12mm motorized lens, dark gray housing



### Features

- Supports up to full HD 1080p resolution @ 30fps
- Built-in standard PoE (IEEE 802.3af)
- Supports H.264 and MJPEG codecs
- Built-in high power IR LED's
- 98' IR range (depending on scene reflection)
- IP67 compliant, weather resistant
- Junction box included for convenience
- Conformant with ONVIF Profile S
- 5 year warranty



Included Junction Box



### Camera Specifications

Image Sensor	Progressive scan 1/2.9" CMOS, 2MP
Effective Pixels	1944(H)x1104(V)
Maximum Resolution	1920 x 1080
Minimum Illumination	0 lux
White Balance	ATW/AWB
Compensation	DWDR
Day/Night	IR Cut-filter
Electronic Shutter Speed	1/30 ~ 1/10000 sec
DNR	3D

### Video Specifications

Main Resolution	1920x1080 / 1280x720 @ 30fps
Compression	H.264 (HP/MP), MJPEG (sub stream)
Bitrate Control	VBR, CBR
Multiple Streaming	3 streams

### Audio Specifications

Mono Input	N/A
Mono Output	N/A

### External Terminal Specifications

Ethernet	10/100 Mbps
Power	DC jack

### Network Specifications

Protocols	HTTP, HTTPS, FTP, SMTP, UPnP, DNS, DDNS, NTP, RTSP, RTP, TCP, UDP, ICMP, DHCP
DDNS support	Speco DDNS (free of charge)
Security	Password Protection, User access log, HTTPS encryption
User Access	Max. 8 simultaneous users. Actual number of users may vary depending on bandwidth

### System Specifications

PoE	Standard (IEEE 802.3af)
Alarm Triggers	Motion detection
Alarm Events	FTP upload, email upload
Image Settings	Corridor view in H.264 (90degree/ 270degree)

### Client Specifications

Web Browser Support	Windows (up to Internet Explorer 11)
PC Application	SecureGuard® VMS
Mobile	SecureGuard® Client (iPhone® and Android™)
Embedded Recorder	Speco NVRs/Hybrids, ONVIF Profile S conformant recorders

### Operating & Unit Specifications

Power	PoE, 12VDC (power supply not included)
Power Consumption	7W (max)
Operating Temperature	-40°F - 140°F
Operating Humidity	0% - 90% relative humidity
Unit Dimensions	3.4"(W) x 10.7"(L)
Unit Weight	1.22 lbs
Certifications	FCC, RoHS
Country of Origin	Made in Korea

### Optional Accessories



POEINJ  
12.95W  
PoE Injector



PSW5  
12VDC  
Power Supply

\* Effective on all new purchases as of 2/1/17. ONVIF® is a trademark of Onvif, Inc. Chrome and Firefox use Java which requires an initial internet connection. Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Android, Google Play and the Google Play logo are trademarks of Google Inc. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 4/24/19

