

27MK600M-B.AUS

27" 3-Side Virtually Borderless IPS FHD Monitor

27" FHD (1920 x 1080) IPS Display

3-Side Virtually Borderless Design

Radeon FreeSync™ Technology

Dual HDMI

On Screen Control



PICTURE QUALITY	
Screen Size	27" Flat
Panel Type	IPS
Color Gamut (CIE1931)	NTSC 72% (CIE1931)
Color Depth(Number of Colors)	16.7M colors
Pixel Pitch(mm)	0.3114 mm x 0.3114 mm
Response Time (GTG)	5ms(Faster)
Refresh Rate	75Hz
Aspect Ratio	16:9
Resolution	1920 x 1080
Brightness	250cd/m ² (Typ.) 200cd/m ² (Min.)
Contrast Ratio	1000:1 (Typ.) Mega
Viewing Angle	178/178
Surface Treatment	Anti glare,3H
INPUT/OUTPUT	
HDMI	Yes x 2
D-Sub	Yes
Headphone Out	Yes
POWER	
Type	Adapter
Input	100-240, (50/60Hz)
Output	19V/1.3A
Normal On (EPA Typ.)	20.3W
Normal On (factory out condition Typ.)	25.5W
Power Save/Sleep Mode (Max)	0.3W
DC Off (Max)	0.3W

SPECIAL FEATURES	
Picture Mode	Custom, Reader, Color Weakness, Photo, Cinema, Game
Ratio	Wide/Original
DDC/CI	Yes
HDCP	Yes
Plug & Play	Yes
Response Time Control	Yes
Color Calibrated	Yes
Adaptive Sync	Radeon FreeSync™
DAS Mode	Yes
Black Stabilizer	Yes
Crosshair	Yes
Flicker Safe	Yes
Automatic Standby	Yes
Smart Energy Saving	Yes
Super Resolution+	Yes
On Screen Control (OSC)	Yes
Black Level	Yes
DFC	Yes
Gamma Control	Yes
Color Temperature	Yes
R/G/B Color Control	Yes
OSD Lock	Yes
Auto Adjustment(D-sub Only)	Yes
SOUND	
Speaker	No built-in speaker
DIMENSIONS/WEIGHT	
With Stand (WxHxD)	24.1" x 17.9" x 8.2"
Without Stand (WxHxD)	24.1" x 14.3" x 2.9"
Shipping Dimensions (WxHxD)	27.2" x 17.0" x 5"
With Stand Weight	10.6 lbs
Without Stand Weight	9.5 lbs
Shipping Weight	13.5 lbs
STAND	
Tilt(Angle)	-5-15
CABINET / ACCESSORIES	
Wall Mount Size (mm)	100 x 100
Power Cord	Option
HDMI	Yes
S/W Install CD	Yes
Easy Setup Guide	Yes
Manual	Yes
STANDARD	
UL(cUL)	Yes
TUV-Type	Yes
FCC-B, CE	Yes
CCC (for China)	Yes
KC	Yes
VCCI	Yes
EPA 7.0	Yes
ErP	Yes
Windows 10	Yes
LIMITED WARRANTY / UPC	
Limited Warranty	1 Year Parts and Labor
UPC	719192622470
Country of Origin	China