



FEATURE



Frameless Design

With the narrow bezel, you will not even notice the monitor at all in the heat of the moment.



Wide Color Gamut

Game colors and details will look more realistic and refined, to push game immersion to its limits.



Radeon FreeSync™

Puts an end to choppy gameplay and broken frames with fluid, artifact-free performance at virtually any framerate.



165Hz High Refresh Rate

Experience smooth gaming with a blazing fast 165Hz refresh rate, that gives you the upperhand in fast moving games



1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



Curved Gaming

MSI Curved Gaming Monitor will give you the most immersive and competitive edge you need to take down your opponents.

CONNECTIONS



- 1. 5-way joystick navigator
- 2. 1x DC Jack
- 3. 2x HDMI 1.4b
- 4. 1x Display Port 1.2a
- 5. 1x Earphone out
- 6. 1x Kensington lock

SPECIFICATION

DCI-P3 / sRGB	90% / 115%
Panel Size	27" (69cm)
Aspect ratio	16:9
Panel Resolution	1920 x 1080 (FHD)
Pixel Pitch (H x V)	0.3114(H) x 0.3114(V)
Refresh Rate	165Hz
Response time	1ms
Viewing angle	178° (H) / 178° (V)
Curved	1500R
Brightness	250 nits
Contrast Ratio	3000:1
Power consumption	45W
Control	5-way OSD navigation joystick
Dimension (W x H x D)	611.5 x 457.9 x 225.4 mm / 24.08 x 18.23 x 8.87 inch
Frameless Design	Yes
Weight	5.4kg / 9.0kg 11.9lbs / 19.84lbs
DCR	100000000:1
Active Display Area (mm)	597.888(H) x 336.312(V)
Surface Treatment	Anti-glare
Display Colors	16.7M
Video ports	1x DP (1.2a) 2x HDMI (1.4b)
Audio ports	1x Earphone out
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Power Type	External Adaptor 20V/2.25A (up to 45W)
Power Input	100~240V, 50~60Hz
Signal Frequency	53.28 to 183.15KHz (H) 48 to 165Hz (V)
Adjustment (Tilt)	-5° ~ 20°
Note	Display Port: 1920 x 1080 (Up to 165Hz) HDMI: 1920 x 1080 (Up to 144Hz)
Panel Type	Samsung VA