

GCS22DPKIT

## 2-Port VGA and DisplayPort KVM Switch Kit




- Switch between two computers with the push of a button
- Offers the flexibility to mix and match VGA & DisplayPort computer connections
- Includes 2 x DisplayPort to VGA adapters
- No external power needed
- Cost effective, Plug-N-Play solution, no software needed

### 2-Port Cable VGA & DisplayPort KVM Switch


- Switch between two computers with the push of a button
  - Offers the flexibility to mix and match VGA & DisplayPort computer connections
  - Includes 2 x DisplayPort to VGA adapters
  - No external power needed
  - Cost effective, Plug-N-Play solution
- 
- Switch between two computers with the push of a button
  - Offers the flexibility to mix and match VGA & DisplayPort computer connections
  - Includes 2 x DisplayPort to VGA adapters
  - No external power needed
  - Cost effective, Plug-N-Play solution, no software needed
  - One USB keyboard, USB mouse, and VGA monitor controls two computers
  - Max resolution: 2048 x 1536, DDC2B
  - 4' Long molded-in cables to simplify setup
  - Compatible with PC, MAC and SUN operating platforms
  - Supports Windows7 or higher, Mac OS 9.0 or higher, Sun Solaris 9 or higher
  - Full Mac keyboard support
- 
- Supports programmable mice
  - All cables included
  - 2 x DisplayPort to VGA Adapters convert your DisplayPort to VGA:
    - Works with computer systems using DisplayPort
    - Compliant with Displayport Specification 1.1a for both 1.62 Gbps and 2.7 Gbps
    - Support full DisplayPort link tracking
    - Supported resolutions:
      - Full HD 1080p
      - 1920 x 1200
      - VGA, SVGA, XGA, SXGA and UXGA at 162 MHz pixel rate
    - Support interrupt request output for expansion function
    - Support Deep Sleep Mode (suspend mode)



**Solution 1**



**Solution 2**



**Requirements**

**Package Contents**

- **Console:**
- 1 x VGA display
- 1 x standard 104 key wired USB keyboard
- 1 x standard 2 or 3 button wired USB mouse
- 
- **Computers:**
- VGA or DisplayPort port
- USB ports
- 3.5mm audio port (optional)
- 
- **Operating Systems:**
- Windows Vista®, Windows® 7, Windows® 8.1, Windows® 10
- Mac® OS 9 to 10.x
- Oracle® Solaris
- Linux®, Unix and other USB supported systems\*

\*Additional drivers and support may be needed

## Specifications

Function	GCS22DPKIT	Dimensions	GCS22DPKIT
<b>Computer Connections</b>		<b>POP Information</b>	
Direct	2	10" Peg Hook	3
<b>Console Connectors</b>		<b>Unit Dimensions</b>	
Monitor	VGA	Height	12.5" (31.75cm)
Keyboard	USB	Depth	0.87" (2.2cm)
Mouse	USB	Length	2.5" (6.35cm)
<b>CPU Connectors</b>		<b>Unit Package Dimensions</b>	
Monitor	2 x VGA; 2 x DisplayPort (with adapters)	Width	7.4" (18.7cm)
Keyboard & Mouse	2 x USB	Height	7.6" (19.3cm)
<b>LEDs</b>		Depth	2.25" (5.7cm)
On Line	Green	<b>Master Carton</b>	
<b>Video Resolution</b>	up to 2048x1536 (VGA), up to 1920x1200 (with adapters)	Width	6.5" (16.5cm)
<b>Port Selection</b>	Remote Pushbutton	Height	7.9" (13cm)
<b>Cable Length</b>	2 x 4ft KVM, 1 x 6ft Remote Pushbutton	Depth	14.9" (37.9cm)
<b>Cable Type</b>	Bonded USB KVM	Master Carton Qty.	6
<b>Housing</b>		<b>Weight</b>	
Case	Plastic	Master Carton Wt.	7.7lb (3.5kg)
		Unit Pack Wt.	1.2lb (0.54kg)
		Unit Wt.	0.875lb (0.39kg)