

LED A Series Posters LED-A019i and LED-A025i (1.9mm and 2.5mm A Series Indoor)



LED A Series Posters: Powerful, Simple, Versatile

The NECA Series poster is a plug and play solution designed for easy setup for a wide array of applications. The LED Posters come in 2 pixel pitches (1.9mm and 2.5mm) providing optimum clarity regardless of viewing distance. With a depth of just 35mm, plus complete internal cabling, the A series presents a sleek profile for a bezel-free viewing experience. With excellent viewing angles, consistent vibrant colors and superb brightness; the A Series delivers content that gets noticed. The plug and play design with built in media player makes

it quick and easy to setup or change content. The A series posters are ideal for a variety of applications including: rental, retail, restaurant, transportation, and much more.

Benefits

All-in-one design – Fast and easy setup with built-in media player

Ultimate Versatility – Multiple setup options with included floor stand, hanging mount, as well as ability to cascade multiple displays together

Lightweight and thin – 65lbs/ 35mm for easy transportation and setup

Excellent Homogeneity – uniform color and brightness across the entire display

Outstanding Picture Quality – Through use of Multi-Color LEDs, for clear images, even in the brightest environments



LED A Series Posters LED-A019i and LED-A025i (1.9mm and 2.5mm A Series Indoor) - Technical Specification

Direct View LED Kit		LED-A019i	LED-A025i
Display	Panel Technology	Direct View LED	Direct View LED
	Pixel Configuration	3-1 SMD (Black)	3-1 SMD (Black)
	Panel Resolution	288 x 972	224 x 756
	Pixel Pitch	1.944mm	2.5mm
	Brightness (Max)	1100 cd/m²	1100 cd/m²
	Contrast Ratio (typical)	4500:1	4500:1
	Viewing Angle (typical)	75/75 horizontal / 70/70 vertical	75/75 horizontal / 70/70 vertical
	Dimming Capability	256 levels	256 levels
	Color Processing	Up to 13 bit	Up to 13 bit
	Displayable Colors	281 Trillion	281 Trillion
	Refresh Rate	2880Hz	2880Hz
Connectivity	Input Terminals	HDMI	HDMI
	External Control	RJ-45	RJ-45
Power Consumption	On (typical)	520 Watts	520 Watts
Physical Dimensions	Dimensions (W x H x D)	22.5 x 74.9 x 1.4 in. / 572 x 1902 x 35mm	22.5 x 74.9 x 1.4 in. / 572 x 1902 x 35mm
	Weight (Net)	65 lbs. / 29.5 kg	65 lbs. / 29.5 kg
Environmental Conditions	Operating Temperature	-4-95°F / -20-35°C	-4-95°F / -20-35°C
	Operating Humidity	10-80%	10-80%
	Operating Altitude	16404 ft. / 5000m	16404 ft. / 5000m
	Storage Temperature	-4-140°F / -10-60°C	-4-140°F / -10-60°C
	Storage Humidity	10-85%	10-85%
	Storage Altitude	16,404 ft. / 5000m	16,404 ft. / 5000m
	IP Rating	IP20	IP20
Ships With		Hanging Mount, Floor Stand, Setup Sheet, HDMI Cable, Power Cord, Wireless LAN Antenna	Hanging Mount, Floor Stand, Setup Sheet, HDMI Cable, Power Cord, Wireless LAN Antenna
Limited Warranty		2 Years	2 Years

All rights reserved in favor of their respective owners. All hardware and software names are brand names and/or registered trademarks of the respective manufacturers. All specifications are subject to change without notice.