



A Commercial Grade Chrome Tablet




The Chromebook Commercial Tab is AOPENs' first hand-held device. This tablet is specially designed for commercial environments and functions as logistical system in transportation, ordering system in QSR or hospitality or patient logs in healthcare. This Chromebook Commercial Tab is unique from other tablets for one reason only: It's ruggedised!

The features:

- + High Graphics & Quality Video Playback - 9.7" QXGA IPS touch screen / Resolution 2048 x 1536
- + High Performance - Hexa-core (Cortex A72 x 2, A53 x 4) / Processor with 1.6Hz (Up to 2.0GHz)
- + Ruggedized Design - Drop tested Military Grade: MIL STD 810G-516.6 with 26 drops from 4 feet (48 Inch, hand-held height)
- + User-friendly Design - Hand strap support / Kick stand (Option) / Shoulder strap (Option)
- + Secure Design – Google TPM / Customised power bottom with kiosk mode / Kensington Lock
- + Commercial Accessories - Supports Standard VESA accessories to adopt to working scenarios
- + All Day Productivity – Battery life up to 10 hours
- + Wacom Stylus Pen



Chrome



Model name	Chomebook Commercial Tab
System Specifications	OS : Chrome
	9.7" IPS
	Display Orientation : Landscape/ Portrait
	Dimension (set) : 247 (L) x 180 (W) x 19 (H)mm (w/o hand strape)
	Weight (Net) : 685g
	Housing : Plastic/ TPU , Black
	Camera: Front 5M pixel, rear 2M pixel
	1W Speaker x 2
	Single I2S Digital MIC x 1
	Gyro-Sensor
Protector	TPM: Google-Heaven-H1
	Drop tested : MIL-STD-810G (122cm/ 48")
	Mounting : VESA 100 x 100mm
LCD Panel	Material : Plastic/ TPE
	Resolution: 2048 x 1536
	Brightness : 300nits
Touch Panel	Aspect Ratio : 4:3
	Surface Hardness : 9H
	Project Capacitive Touch 10 points
Computing	CPU : RK3399 (ARM based 2.0GHz)
	Graphic: Mali-T864
	Memory : LPDDR3 4GB
	Storage : EMMC 5.1 32GB
	LAN : 802.11 b/ g/ n/ ac + BT4.2 x 1
I/O	Combo headphone/Speaker jack (Hidden)
	USB3.0 x 1 Type C
	MicroSD Reader x 1 (Hidden)
	Power Button x 1
	Volume Button x 1
Stylus Type	Wacom EMR-W9013
	With Pen Detect Switch
Power Supply	DC Adapter Type C 45W
Battery	8860 mAh (Battery life: around 10 hours)
Warranty	1 year
Temperature	Operating : 0 to 35 °C
Humidity	90% RH max

Supports:

