

# Hybrid monitor

**22"**  
Screen Size

**1920x1080**  
Native Resolution

**24  
7365**  
Built to run 24 x 7 x 365  
Continuously  
Built to Run 24x7x365

**HDMI**  
HDMI Input



# 22RDHY

## SPECIFICATIONS


22RDHY	
<b>Display</b>	
Screen Size	21.5 Inch
Max. Resolution	1920 x 1080
Brightness	250cd/m <sup>2</sup>
Contrast Ratio	1000 : 1
Aspect Ratio	16 : 9
Viewing Angle (H/V)	178° / 178°
Display Color	16.7 Million
Response Time	< 5ms (Gray to Gray)
TV Lines	1000Lines
<b>Interface</b>	
Inputs	2xHD Analogue(TVI/AHD/CVI), 1xHDMI
Outputs	2xHD Analogue(TVI/AHD/CVI)
HDMI (VESA)	800x600/1024x768/1280x720/1280x1024/1366x768/1440x900/1600x1200@60HZ, 1920x1080@25/30/50/60HZ, 2560x1440@30/60
HD Analogue	TVI:720P@25/30fps,1080P@25/30fps,2560x1440@25/30fps,5MP@20fps,4MP@25fps,3MP@18.75fps, CVI:720P@25/30/50/60fps, 1080P@25/30fps, 2560X1440@25/30fps,4PM@25fps AHD:720P@25/30fps,1080P@25/30fps,2560x1440@25/30fps, 5MP@20fps, 4MP@25fps
<b>Features</b>	
Auto adjustment	Yes
OSD Control	Yes
Multi Language	English,Spanish,Italian,German,French,Polish,Russia,Dutch,Danish
<b>General</b>	
W x H x D (With Stand)	490 x 358.96 x147mm / 4.5kgs
Power consumption	<21W
Working Temp	0~40 °C
Accessories	Power cord, Adapter, Stand, User's guide, HDMI cable
Certificate	FCC-DOC, CE, ROHS

## FEATURES

- ▶ Robust Metal+ Plastic Housing
- ▶ 1920 x 1080p FULL HD
- ▶ HDMI+2xHD Analogue in+2xHD Analogue out
- ▶ TVI/CVI/AHD/CVBS Signals Auto recognition to ONE BNC Port
- ▶ Support 5MP TVI, 4MP CVI, 5MP AHD
- ▶ LED BACKLIGHT



## INTERFACE



- A** HD / ANALOGUE 1 In / Out
- B** HD / ANALOGUE 2 In / Out
- C** HDMI In
- D** DC 12V

\*Design and specifications are subject to change without notice