




ideal™ 2604

Powerful shredder with ECC (Electronic Capacity Control) indicator and an automatic oiler on cross-cut models.



shred volume:	26 gal
feed opening:	10 1/4"
power supply:	115v
max horsepower:	1
dimensions:	19 1/2"w x 18 1/2"d x 36 1/2"h
shipping weight:	123 lbs

simply
ideal.

	2604 strip-cut IDEDSH0360H	2604 cross-cut IDEDSH03620H	2604 cross-cut IDEDSH03610H	2604 super micro-cut IDEDSH0364H
security level:	P-2	P-4	P-5	P-7
strip width / particle size:	3/16"	3/16 x 1 1/2"	3/32 x 5/8"	1/32 x 3/16"
sheet capacity:	27 - 30*	23 - 25*	14 - 16*	6 - 8*
shred capabilities:				paper only
oiler:	no	yes	yes	yes

*Certified using 8 1/2 x 11" 20-lb bond paper and recommended power supply.



centralized office shredder features



safe shredding of CDs / DVDs

On CD-capable models, the electronically controlled shield protects the operator from stray splinters of plastic.



automatic oil injection

On oiler-equipped models, the cutting shafts are automatically lubricated while shredding, ensuring optimal performance.



environmentally friendly bin

Durable, lightweight shred bins can be used with or without disposable bags.



capacity indicator

Patented Electronic Capacity Control (ECC) indicator monitors sheet-capacity levels during operation to prevent jams.



patented safety shield

Electronically controlled transparent safety shield keeps fingers, ties, and other objects away from the cutting shafts.



easy switch

Multifunction control element uses optical signals to indicate operational status, and functions as an emergency stop switch.



1) Super micro-cut shafts and wheels are covered by a one-year warranty.

ideal™

817 W. Peachtree Street NE, Suite 450, Atlanta, GA 30308
 800-826-0161
 help@simplyideal.net
 simplyideal.net