

ASUS ZenBook 14

The world's most compact 14" laptop, with ScreenPad™ 2.0

14" For Business travelers | Young Professionals



NanoEdge
95% S/B ratio

ScreenPad™
2.0

3D IR camera for
face login

Super light,
only 1.22kg

Discrete
graphics

All-day
battery life

Military
grade quality

The Intelligent touchpad, evolved

Powered by the new ScreenXpert software, ScreenPad™ 2.0 now has a larger 5.65-inch touchscreen that offers many new features and benefits. This interactive secondary screen enhances productivity, allowing for more efficient workflow. The revised smartphone like interface is more intuitive for improved ease of use. Third party developers can also use ASUS API to optimize their software and user experiences for ScreenPad. The hardware is now also more energy efficient than its predecessor, allowing for 2.5X longer battery life when ScreenPad is in use.

*Specification may vary by model and region.

Powered by Intel® Core™ i7 processor. <https://www.asus.com/Laptops/ZenBook-Series-Home/>

Intel, the Intel Logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation or its subsidiaries in the U.S. and/or other countries.



The most compact design ever

ZenBook 14 heralds a new era of ultraportable design, with an ultracompact, ultralight chassis. Featuring the four-sided NanoEdge display, ZenBook 14 is one of the world's smallest 14-inch laptop and is 13% smaller than the previous generation ZenBook 14 (UX430) — so you can explore your creative vision anywhere!



Unbounded beauty

Designed to give you more screen area in less physical space, the NanoEdge design has slimmer bezels on all four sides to make any visuals more immersive, with less distraction for your eyes. It also features wide-view technology for clear images even when viewed from extreme angles. ZenBook 14 has a crisp, clear, FHD resolution display that makes any visuals look their best, with wide viewing angles and vivid, accurate colors.



ASUS ZenBook 14 (UX434FL)


- Up to 8th gen Intel® Core™ i7-8565U processor
- Windows 10 Pro
- NVIDIA GeForce MX250 2GB GDDR5 VRAM
- 4-sided NanoEdge display with up to 92% screen-to-body ratio
- 14" 16:9 FHD (1920 x 1080) display
- Up to 16G LPDDR3 RAM (2133MHz)
- Ultra-fast up to 1TB SSD
- Revolutionary ScreenPad™ 2.0
- 3D IR Camera
- Harman/Kardon certified speakers

- Interface: 1 x USB 3.1 Type-C, 1 x USB 3.1 Type A, 1 x USB 2.0, 1 x HDMI, 1 x MicroSD Card reader, 1 x Combo audio jack
- Dual-band 802.11ac gigabit-class Wi-Fi 5
- Built-in Bluetooth™ 5.0
- Up to 12.3 hours of battery life with 50 Whs battery
- Full-size backlit keyboard with 1.4mm key travel distance
- Exclusive colors: Royal Blue
- Military-grade quality: MIL-STD 810G standard
- 2 years global warranty

starting at \$ xxxxxxxx

*Specification may vary by model.

ASUS ZenBook 14 ▶▶▶



UX434 FL	
CPU	Intel® Core™ i7-8565U processor 1.8 GHz (8M Cache, up to 4.6 GHz) Intel® Core™ i5-8265U processor 1.6 GHz (6M Cache, up to 3.9 GHz)
Operating System	Windows 10 Home Windows 10 Pro (ASUS recommends Windows 10 Pro) ENDLESS
On board memory	NA
Memory Slot	2
Memory Max.	8GB / 16GB 2133MHz LPDDR3
Storage	1TB PCIe® x4 SSD PCIe® Gen 3 X2 256/512GB SSD
EMMC / ISSD	NA
Display	14", FHD 1920x 1080, sRGB: 100% (NTSC: 72%), Wide view Four-sided NanoEdge design with 92% screen-to-body ratio
Touch Panel	Optional
External Video Display Modes	HDMI 2.0
Discrete GPU	NVIDIA® GeForce® MX250 2GB GDDR5 VRAM
Integrated GPU	Intel® UHD Graphics 620
Video Memory	2GB GDDR5
Video Camera	3D IR HD camera
FingerPrint	NA
Wireless	Dual-band gigabit-class Wi-Fi 5 (802.11ac) + Bluetooth® 5.0
LAN	NA
Card Reader	MicroSD card reader
Interface	1 x USB 3.1 Gen 2 Type-C™ (up to 10Gbps) 1 x USB 3.1 Gen 2 Type-A (up to 10Gbps) 1 x USB 2.0 1 x Standard HDMI 1 x MicroSD card reader 1 x Audio combo jack 1 x DC-in
Audio	Certified by Harman/Kardon Built-in array microphone
Weight (kg)	1.26 kg
Dimension (cm)	31.9 x 19.9 x 1.69 cm (WxDxH)
AC Adapter	65W AC Adapter: Output: 19V DC, 65W; Input: 100~240V AC; 50/60Hz universal
Battery	50Wh 3-cell lithium-polymer battery
Replaceable Battery	NO
Keyboard Type	Illuminated Chiclet Keyboard
Security	3D IR camera for face login MIL-STD 810G tested
warranty	
Price	