

GUD3C04

# Access Pro™ 2-Port USB-C KVM Switch with Power Delivery (TAA Compliant)



- 2-Port USB-C KVM Switch with Power Delivery
- Control and share 2 USB-C devices with DP Alt Mode from one keyboard, mouse, and an HDMI monitor
- Power Delivery<sup>1</sup> (USB-C external power needed) with up to 75W charging for laptop<sup>2</sup> and up to 10W for smartphone<sup>3</sup>
- Supports Windows, Mac, iPad Pro 2018 (3rd generation), Android 8+ devices

## USB-C KVM - Switch Between Two USB-C Devices

Easily switch between two USB-C devices and control them with one keyboard, one mouse and view content on one 4K monitor. IOGEAR's Access Pro™ 2-Port USB-C KVM Switch requires no software and comes complete with the Power Delivery function, USB-C cables, and a 6-foot push-button remote switch. Why spend extra money on features you don't need? The USB-C KVM offers the most efficient and affordable way to switch between two USB-C or Thunderbolt 3-equipped Macs, PCs, iPads, or Android tablets and smartphones with a single-cable connection to each device without additional drivers or software.

- 2-Port USB-C KVM Switch with Power Delivery
- Control and share 2 USB-C devices with DP Alt Mode from one keyboard, mouse, and an HDMI monitor
- Power Delivery<sup>1</sup> (USB-C external power needed) with up to 75W charging for laptop<sup>2</sup> and up to 10W for smartphone<sup>3</sup>
- Supports Windows, Mac, iPad Pro 2018 (3rd generation), Android 8+ devices
- Resolution up to 4K UHD 3840 x 2160 @30Hz for USB-C laptops
- Resolution up to 1080p @60 for USB-C tablets and smartphones
- Thunderbolt™ 3 laptop compatible
- USB 3.1 Gen1 supports data transfer rates up to 5 Gbps
- Convenient switching between devices via a push-button remote
- Supports DeX® Mode<sup>4</sup> on Samsung USB-C smartphones
- Plug-n-Play; no software or driver needed
- HDCP 1.4 Compliant

Note:


<sup>1</sup>For optimal performance, Limited Power Source (LPS) certified USB-C power adapter

<sup>2</sup>Must be plugged into Primary USB-C port 1

<sup>3</sup>When plugged into Secondary USB-C port 2

<sup>4</sup>Samsung DeX Mode is only supported on Samsung Galaxy S8, S8+, S9, S9+, S10, S10+, and Note 8, Note 9, and Tab S4; other Android devices support mirror screen





### Requirements

### Package Contents

- Sources:
  - USB-C enabled devices with DP-Alt Mode over USB-C
  - USB-C external power source (recommend a Limited Power Source (LPS) certified USB-C power adapter)
- Console:
  - HDMI monitor
  - Standard wired 104 keys USB keyboard
  - Standard wired 2 or 3-button USB mouse
- Operations:
  - Windows® 10 (32/64 bit)+
  - MacOS® X 10.12+
  - iPadOS® 12.1+; iPad Pro® 3rd generation (2018)<sup>1</sup>
  - Android 8+<sup>2</sup>

- 2-Port USB-C KVM Switch with Power Delivery
- 2 x 3ft USB-C to USB-C cables
- 1 x 6ft Remote pushbutton
- Quick Start Guide
- Warranty Card

<sup>1</sup>For complete HID keyboard and mouse support, iPadOS 13+ is recommended

<sup>2</sup>DeX Mode is only supported on Samsung Galaxy S8, S8+, S9, S9+, and Note 8, Note 9, and Tab S4 for extended screen; other Android devices support mirror screen

## Specifications

Function	GUD3C04	Dimensions	GUD3C04
<b>Upstream Port</b>		<b>POP Information</b>	
USB-C	1x USB-C for laptop, 1x USB-C for smartphone; data rate up to 5Gbps	10" Peg Hook	3
<b>Downstream Port</b>		6" Peg Hook	2
HDMI	1x HDMI 1.4b compliant, up to 4K UHD 3840 x 2160 @30Hz resolution	<b>Unit Dimensions</b>	
USB-A	2x USB-A 3.1 Gen 1, data rate up to 5Gbps	Height	0.9" (2.29cm)
USB-C	1x USB-C for Power Delivery Pass-Thru	Depth	4.75" (12.07cm)
<b>Power</b>		Length	5.75" (14.6cm)
Power Delivery Pass-Thru	Support USB PD 2.0 at 5V/9V/15V/20V up to 85W for laptop charging.* Provides 5V/2A for Smartphone charging.*	<b>Unit Package Dimensions</b>	
<b>Power Consumption</b>		Width	6.1" (15.5cm)
	5V/3A (15W)	Height	7.28" (18.5cm) + 1.5" (3.8cm) hanging tab
<b>Operating System Requirements</b>		Depth	2.16" (5.5cm)
Mac	MacOS X 10.12 and above	<b>Master Carton</b>	
Windows	Windows 10 (32/64 bit) and above	Width	15.16" (38.5cm)
Android	Android 7 and above	Height	7.87" (20cm)
<b>Environment</b>		Depth	6.69" (17cm)
Humidity	0?80% RH, Non-condensing	Master Carton Qty.	6
Operation Temperature	32 - 104°F (0?40°C)	<b>Weight</b>	
Storage Temperature	-4 - 140°F (-20?60°C)	Master Carton Wt.	8.9lb (4.05kg)
		Unit Pack Wt.	1.4lb (0.64kg)
		Unit Wt.	0.8lb (0.36kg)