

DH9 Series

ALL IN ONE PC



PROCESSOR	Intel® Braswell® N3060 1.6 GHz dual core / Broadwell-U i3-5005U 2 GHz (optional)	
MEMORY	DDR3L 1600 MHz x 1, 8 GB max	
VIDEO GRAPHICS	Intel® HD graphics	
VIDEO OUTPUT	HDMI x 1	
AUDIO	Realtek ALC269, 2 channel HD audio	
WEBCAM	2.0M pixel & internal MIC	
TOUCH SCREEN	19.5", 16:9 wide LCD panel, 1600 x 900 px, multi-touch screen (10 point)	
WIRELESS LAN	Intel 3165, Supports 802.11 b/g/n/ac + Bluetooth 4.2	
ETHERNET	RTL8411BN CG 10/100/1000 MB/s operation	Supports Wake on LAN function & VLAN tagging
STORAGE INTERFACE	SATA 6 GB/s interface, 2.5" HDD/SSD x 1 (optional)	
FRONT & TOP PANEL	(1) SD Card Reader (1) Webcam (1) Microphone (1) Stereo speaker	(1) Power Button (1) HDD LED (1) Brightness Control
LEFT PANEL	(1) Thermal vent (1) USB 3.0 port (1) USB 2.0 port	(1) LAN port (1) HDMI (1) DC-in
RIGHT PANEL	(1) Slim 9.5 mm DVD-RW (optional)	
BACK PANEL	(4) USB 2.0 ports (1) Headphone/Line-out	(1) MIC-in jack (2) Kensington Lock
DIMENSIONS	19.1(L) x 1.6(W) x 13.5(H) inches	
POWER	Input: 100 - 240V AC Power Plug region specific	65W power adapter
ACCESSORIES	VESA mounting plate (optional) 65W power adapter	OS recovery disk
CONNECTORS	(1) SATA, (1) LPC, (1) Fan connector, (1) USB connector	
ODD	ODD add-on option supported	
BATTERY	4 cell battery (optional)	
OPERATING SYSTEM	Windows 10 (DH9U/DH9UB), Linux (DH9UB)	
BIOS	Supports PnP, ACPI 3.0, Supports external USB flash memory card boot up	

For more information on all products, please contact us at sales@us.shuttle.com or 626.820.9000

© 2019 Shuttle Computer Group, Inc. All rights reserved. Specifications are subject to change without notice. Not responsible for any photographic or typographic errors. Photos shown may vary from actual look. Intel, the Intel logo, and Intel Core are trademarks of Intel Corporation or its subsidiaries in the US and/or other countries. ©Intel Corporation

DH9 Series

ALL IN ONE PC

Front View and Left Side View



- | | |
|---|------------------------|
| F1 Webcam | L1 Thermal vent |
| F2 Microphone | L2 USB 3.0 port |
| F3 Touchscreen | L3 USB 2.0 port |
| F4 Power Button/HDD LED/
Brightness control | L4 LAN port |
| F5 Stereo Speaker | L5 HDMI port |
| | L6 DC-in |

For more information on all products, please contact us at sales@us.shuttle.com or 626.820.9000

© 2019 Shuttle Computer Group, Inc. All rights reserved. Specifications are subject to change without notice. Not responsible for any photographic or typographic errors. Photos shown may vary from actual look. Intel, the Intel logo, and Intel Core are trademarks of Intel Corporation or its subsidiaries in the US and/or other countries. ©Intel Corporation

DH9 Series

ALL IN ONE PC

Back and Right Side View



- B1** SD Card Reader
- B2** Stand
- B3** Headphone/MIC jack
- B4** USB 2.0 x 4 ports
- B5** Kensington Lock

- R1** Optional ODD (Optical Disk Drive)

For more information on all products, please contact us at sales@us.shuttle.com or 626.820.9000

© 2019 Shuttle Computer Group, Inc. All rights reserved. Specifications are subject to change without notice. Not responsible for any photographic or typographic errors. Photos shown may vary from actual look. Intel, the Intel logo, and Intel Core are trademarks of Intel Corporation or its subsidiaries in the US and/or other countries. ©Intel Corporation

DH9 Series

ALL IN ONE PC



EQUIPPED WITH INTEL® BRASWELL

The DH9 is equipped with an Intel® Braswell® N3060 1.6 GHz dual core processor* with a max TDP of 15W. With DDR3L 1600 MHz memory support and built in HD graphics, it can play Full HD/1080P resolution video.

*Intel® Broadwell-U i3-5005U configuration available



MULTI-TOUCH

MULTI-TOUCH SCREEN


A 19.5" high definition LCD display with 10-point multi-touch functionality utilizes capacitive technology for bright viewing, responsive touch, and high level of color accuracy.



VESA MOUNT

VESA MOUNTABLE


With VESA mount compatibility the DH9 can provide touchscreen interaction for a variety of commercial applications.



BATTERY OPTION

RECHARGABLE BATTERY OPTION

A rechargeable backup battery option provides up to two hours of power in case of sudden power outages.



SATA 6G

HIGH-SPEED STORAGE INTERFACE

The DH9 provides SATA 6G with support for one 2.5" SATA HDD/SSD (7mm to 9mm size) to significantly increase system data transmission performance.

For more information on all products, please contact us at sales@us.shuttle.com or 626.820.9000

© 2019 Shuttle Computer Group, Inc. All rights reserved. Specifications are subject to change without notice. Not responsible for any photographic or typographic errors. Photos shown may vary from actual look. Intel, the Intel logo, and Intel Core are trademarks of Intel Corporation or its subsidiaries in the US and/or other countries. ©Intel Corporation