




EXTERNAL SSD

SPECIFICATIONS

Capacity	256GB / 512GB / 1TB / 2TB
Interface:	USB 3.1 Type-C
Platforms Supported:	Android Phone / Android Tablet / PC / Laptops / Desktops
Dimensions:	2.68" x 2.68" x 0.44"
Weight:	0.08 lbs
Max.Read Speed:	Up to 450MB/s
Max.Write Speed:	Up to 400 MB/s
Material:	ABS + PP
Color:	Midnight Black, Pearl White, Candy Red Apple, Rose Gold
Working Indicator :	White light
Accessible Platform:	Win/Mac/Android 4.0 or above
Limited Warranty Period:	5 Years
Working Temperature:	0 °C to +40 °C



Huge
Capacity



High-Speed
Transmission




Portable
Design



Shock
Resistant



Expansion
Mobile Phone



Includes Cables:
USB-C to C / USB-C to A