

Cisco QSFP-40G-CSR4 Compatible QSFP+ Module - 40GBASE-SR4 - 40GbE Multimode Fiber MMF Optic Transceiver - 40GE Gigabit Ethernet QSFP+ - MPO 300m - 850nm - DDM Cisco Firepower, ASR9000, ASR1000

Product ID: QSFP-40G-CSR4-ST



The QSFP-40G-CSR4-ST is a Cisco QSFP-40G-CSR4 compatible fiber transceiver module that has been designed, programmed and tested to work with Arista Networks brand switches and routers. It delivers dependable 40 GbE connectivity over fiber cable, for 40GBase-SR4 compliant networks, with a maximum distance of up to 400 m (1312 ft.).

Technical Specifications:

- **Wavelength:** 850nm
- **Maximum Data Transfer Rate:** 40 Gbps
- **Type:** Multi Mode
- **Connection Type:** MPO
- **Maximum Transfer Distance:** 400 m (1312 ft.)

- **MTBF:** 95,832,027 hours
- **Power Consumption:** Low power consumption
- **Digital Diagnostics Monitoring (DDM):** Yes

This QSFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

StarTech.com SFPs

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Features

- 100% CISCO QSFP-40G-CSR4 COMPATIBLE: Works with Cisco switches like Firepower, ASR9000, ASR1000, C9300, NCS5500 and others
- TECHNICAL SPECS: 40GBASE-SR4 | 40 Gbps | Multi Mode (MMF) | MPO Connector | 850nm | Digital Diagnostic Monitoring (DDM) | Distances up to 300m (984ft)
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in Cisco routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- OUTSTANDING SUPPORT: Backed by StarTech.com for the life of the module itself, not your equipment; our modules won't void your OEM support and with access to our Tech Advisors 5/24
- WORKS WITH MSA COMPLIANT SWITCHES: Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

	Warranty	Lifetime
Hardware	Compatible Brand	Cisco®
Performance	Maximum Data Transfer Rate	40.00 Gbps
Physical Characteristics	Product Height	8.500
	Product Length	0.7 in [1.9 cm]
	Product Width	122.000
	Weight of Product	37.500
Packaging Information	Package Height	35.000
	Package Length	205.000
	Package Width	120.000
	Shipping (Package) Weight	60.000
What's in the Box	Included in Package	1 - QSFP+ Transceiver

Product appearance and specifications are subject to change without notice.