


# Cisco QSFP-40G-SR4-S Compatible QSFP+ Module - 40GBASE-SR4 - 40GbE Multimode Fiber MMF Optic Transceiver - 40GE Gigabit Ethernet QSFP+ - MPO 100m - 850nm - DDM Cisco Firepower, ASR9000, ASR1000

Product ID: QSFP-40G-SR4-S-ST



The QSFP-40G-SR4-S-ST is a Cisco QSFP-40G-SR4-S compatible fiber transceiver module that has been designed, programmed and tested to work with Cisco brand switches and routers. It delivers dependable 40 GbE connectivity over fiber cable, for 40GBase-SR4 compliant networks, with a maximum distance of up to 100 m (328 ft).

## Technical Specifications:

- **Wavelength:** 850nm
- **Maximum Data Transfer Rate:** 40 Gbps
- **Type:** Multi Mode Fiber
- **Connection Type:** MPO Connector
- **Maximum Transfer Distance:** 100 m (328 ft)

- **MTBF:** 244,610,583 hours
- **Power Consumption:** Low power consumption
- **Digital Diagnostics Monitoring (DDM):** Yes

This QSFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

## StarTech.com SFPs

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

### Certifications, Reports and Compatibility



### Features

- 100% CISCO QSFP-40G-SR4-S COMPATIBLE: Works with Cisco switches like Firepower, ASR9000, ASR1000, C9300, NCS5500 and others
- TECHNICAL SPECS: 40GBASE-SR4 | 40 Gbps | Multi Mode (MMF) | MPO Connector | 850nm | Digital Diagnostic Monitoring (DDM) | Distances up to 100m (328ft)
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in Cisco routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- OUTSTANDING SUPPORT: Backed by StarTech.com for the life of the module itself, not your equipment; our modules won't void your OEM support and with access to our Tech Advisors 5/24
- WORKS WITH MSA COMPLIANT SWITCHES: Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

<b>Hardware</b>	Warranty	Lifetime
	Compatible Brand	Cisco
<b>Performance</b>	Maximum Data Transfer Rate	40.00 Gbps
<b>Physical Characteristics</b>	Product Height	8.500
	Product Length	0.7 in [1.9 cm]
	Product Width	122.000
	Weight of Product	37.500
<b>Packaging Information</b>	Package Height	35.000
	Package Length	205.000
	Package Width	120.000
	Shipping (Package) Weight	60.000

Product appearance and specifications are subject to change without notice.