

Cisco SFP-10G-BX-D-60 Compatible Transceiver Module - 10GBASE-BX - 10 Gigabit Ethernet BiDi Fiber Single Strand SFP+ - 60km SM DS DDM Cisco ASR9000, ASR1000, NCS5500

Product ID: SFP-10G-BX-D-60-ST



The SFP-10G-BX-D-60-ST is a Cisco SFP-10G-BX-D-60 compatible downstream fiber SFP+ transceiver which pairs with StarTech.com's SFP-10G-BX-U-60-ST. They are designed, programmed and tested to work with 10GBase-BX compatible Cisco switches and routers. The SFP+ transceiver module supports a maximum distance of up to 60 km (37.3 mi) and delivers dependable 10 GbE connectivity over fiber cabling.

Technical Specifications:

- **Wavelength:** 1330nmTx/1270nmRx
- **Maximum Data Transfer Rate:** 10Gbps
- **Type:** Single Mode Fiber
- **Connection Type:** LC Connector
- **Maximum Transfer Distance:** 60 km (37.3 mi)
- **Power Consumption:** Low power consumption

- **DDM:** Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

StarTech.com SFPs

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP Cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Features

- 100% CISCO SFP-10G-BX-D-60 COMPATIBLE SFP+: 10 GbE BiDi transceiver works with Cisco switches and routers like C9400, C9500, N700, C4900, NCS5500, N9300, N3000, N9500, ASR9000, ASR1000 and others.
- INCREASE BANDWIDTH ON EXISTING INFRASTRUCTURE: This 10 Gigabit Ethernet bi-directional WDM SFP+ transceiver module sends and receives over a single strand of fiber optic cable instead of two.
- TECH SPECS: 10GBASE-BX | 10 Gbps | 10G Bi-Directional downstream single-mode (SM) fiber | LC connector | 1330/1270nm wavelength | Digital Diagnostics Monitoring (DDM) | Distances up to 60km (37.3 mi)
- LIFETIME WARRANTY: Will not void the warranty on your OEM routers and switches. This module is TAA compliant and backed by a Lifetime Warranty and 24/5 technical support based in North America.
- PROGRAMMED & TESTED FOR COMPATIBILITY: Compatible with OEM routers and switches. MSA Compliant with DDM that reports the transceiver's status to most SNMP network management tools.
- Hot-swappable with fiber-optic modules

	Warranty	Lifetime
Hardware	Compatible Brand	Cisco®
Performance	Maximum Data Transfer Rate	10.00 Gbps
	Power Consumption (In Watts)	< 1W
Physical Characteristics	Product Height	12.600
	Product Length	0.5 in [1.4 cm]
	Product Width	58.400
	Weight of Product	24.000
Packaging Information	Package Height	31.000
	Package Length	115.000
	Package Width	90.000
	Shipping (Package) Weight	50.000

Product appearance and specifications are subject to change without notice.