

# Cisco SFP-10G-LR-40 Compatible SFP+ Module - 10GBASE-LR - 10GbE Single Mode Fiber SMF Optic Transceiver - 10GE Gigabit Ethernet SFP+ - LC 40km - 1310nm - DDM Cisco Firepower, ASR9000, ASR1000

Product ID: SFP-10G-LR-40-ST



The SFP-10G-LR-40-ST is a Cisco SFP-10G-LR-40 compatible fiber transceiver module that has been designed, programmed and tested to work with Cisco brand switches and routers. It delivers dependable 10 GbE connectivity over fiber cable, for 10GBase-LR compliant networks, with a maximum distance of up to 40 km (24.8 mi).

## Technical Specifications:

- **Wavelength:** 1310nm
- **Maximum Data Transfer Rate:** 10 Gbps
- **Type:** Single Mode Fiber
- **Connection Type:** LC Connector
- **Maximum Transfer Distance:** 40 km (24.8 mi)

- **MTBF:** 426,514,897 hours
- **Power Consumption:** < 1.6W
- **Digital Diagnostics Monitoring (DDM):** Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

## StarTech.com SFPs

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

### Certifications, Reports and Compatibility



### Features

- 100% CISCO SFP-10G-LR-40 COMPATIBLE: Works with Cisco switches like Firepower, ASR9000, ASR1000, NCS5500, C3850 and others
- TECHNICAL SPECS: 10GBASE-LR | 10 Gbps | Single Mode (SMF) | LC Connector | 1310nm | Digital Diagnostic Monitoring (DDM) | Distances up to 40km (24.8mi)
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in Cisco routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- OUTSTANDING SUPPORT: Backed by StarTech.com for the life of the module itself, not your equipment; our modules won't void your OEM support and with access to our Tech Advisors 5/24
- WORKS WITH MSA COMPLIANT SWITCHES: Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

<b>Hardware</b>	Warranty	Lifetime
	Compatible Brand	Cisco®
	Industry Standards	IEEE 802.3ae 10GBASE-LR
<b>Performance</b>	Maximum Data Transfer Rate	10.00 Gbps
	Power Consumption (In Watts)	< 1.6W
<b>Physical Characteristics</b>	Product Height	13.700
	Product Length	0.5 in [1.4 cm]
	Product Width	58.400
	Weight of Product	21.000
<b>Packaging Information</b>	Package Height	31.000
	Package Length	115.000
	Package Width	90.000
	Shipping (Package) Weight	50.000

Product appearance and specifications are subject to change without notice.