

Juniper SFP-GE40KT13R15 Compatible SFP Module - 1000BASE-BX-U - 10 GbE Gigabit Ethernet BiDi Fiber (SMF) (SFPGE40KT3R5)

Product ID: SFPGE40KT3R5



The SFPGE40KT3R5 is a Juniper SFPP-10GE-SR compatible fiber transceiver module that has been designed, programmed and tested to work with Juniper brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 1000Base-BX40-U compliant networks, with a maximum distance of up to 40 km (24.8 mi).

Technical Specifications:

- **Wavelength:** 1310nmTx/1550nmRx
- **Maximum Data Transfer Rate:** 1000 Mbps (1 Gbps)
- **Type:** Single Mode Fiber
- **Connection Type:** LC Connector
- **Maximum Transfer Distance:** 40 km (24.8 mi)
- **MTBF:** 3,713,222 hours
- **Power Consumption:** < 1.6W
- **Digital Diagnostics Monitoring (DDM):** Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

StarTech.com SFPs

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Features

- **100% JUNIPER SFP-GE40KT13R15 COMPATIBLE:** 1 Gigabit Ethernet BiDi Fiber Single Strand SFP designed, programmed and tested to work with compatible Juniper switches and routers to deliver dependable 1GbE connectivity
- **INCREASE BANDWIDTH ON EXISTING INFRASTRUCTURE:** This 10 Gigabit Ethernet bi-directional WDM SFP+ transceiver module sends and receives over a single strand of fiber optic cable instead of two
- **TECHNICAL SPECS:** 1000BASE-BX-U | 1Gbps | 10G Bi-Directional Upstream | Single Mode (SMF) | LC Connector | 1310nmTx/1550nmRx | Digital Diagnostic Monitoring (DDM) | Distances up to 40km (24.8mi)
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself, not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24
- **PROGRAMMED & TESTED FOR COMPATIBILITY:** Compatible with Juniper routers and switches. MSA Compliant with DDM that reports the transceiver's status to most SNMP network management tools

	Warranty	3 Years
Hardware	Compatible Brand	Juniper
Performance	DDM	Yes
	Maximum Data Transfer Rate	1.00 Gbps
	MTBF	3,713,222 hours
	Wavelength	1310nmTx/1550nmRx
Connector(s)	Connector A	1 - SFP Slot Plug
	Connector B	1 - Fiber Optic LC Simplex Female
Physical Characteristics	Product Height	0.5 in [1.2 cm]
	Product Length	2.6 in [65 mm]
	Product Width	0.6 in [14 mm]
	Weight of Product	2.5 oz [72 g]
Packaging Information	Package Height	0.6 in [15 mm]
	Package Length	9.1 in [230 mm]
	Package Width	8.1 in [207 mm]
	Shipping (Package) Weight	2.8 oz [80 g]
What's in the Box	Included in Package	1 - SFP Transceiver
	Fiber Operating Mode	Full-Duplex
	Max Transfer Distance	40 km (24.8 mi)

Product appearance and specifications are subject to change without notice.