

Dell EMC SFP-10G-LRM Compatible SFP+ Module - 10GBASE-LRM - 10GbE Multimode Fiber MMF Optic Transceiver - 10GE Gigabit Ethernet SFP+ - LC 200m - 1310nm - DDM

Product ID: SFP10GLRMEMS



The SFP10GLRMEMS is a Dell EMC SFP-10G-LRM compatible fiber transceiver module that has been designed, programmed and tested to work with Dell EMC brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 10Base-LRM compliant networks, with a maximum distance of up to 200 m (656 ft).

Technical Specifications:

- **Wavelength:** 1310nm
- **Maximum Data Transfer Rate:** 10 Gbps
- **Type:** Multi Mode Fiber
- **Connection Type:** LC Connector
- **Maximum Transfer Distance:** 200 m (656 ft)
- **MTBF:** 38,631,862 hours
- **Power Consumption:** < 1W

- **Digital Diagnostics Monitoring (DDM):** Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

StarTech.com SFPs

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Features

- **100% DELL EMC SFP-10G-LRM COMPATIBLE SFP+ TRANSCEIVER:** Designed, programmed and tested to work with compatible Dell EMC switches and routers to deliver dependable 10GbE connectivity
- **TECHNICAL SPECS:** 10GBASE-LRM | 10Gbps | Multi Mode (MMF) | LC Connector | 1310nm | Digital Diagnostic Monitoring (DDM) | Distances up to 200m (656ft)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Dell EMC routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24.
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

	Warranty	Lifetime
Hardware	Compatible Brand	Dell EMC
Performance	DDM	Yes
	Fiber Operating Mode	Full-Duplex
	Max Transfer Distance	200 m (656 ft)
	Maximum Data Transfer Rate	10.00 Gbps
	Power Consumption (In Watts)	< 1W
	Wavelength	1310nm
Physical Characteristics	Product Height	12.600
	Product Length	0.5 in [1.4 cm]
	Product Width	58.400
	Weight of Product	30.000
Packaging Information	Package Height	31.000
	Package Length	115.000
	Package Width	90.000
	Shipping (Package) Weight	50.000
What's in the Box	Included in Package	1 - SFP+ Transceiver

Product appearance and specifications are subject to change without notice.