



4MP Dome IP Camera with Junction Box

O4VLD1

2.8mm fixed lens, white housing



Features

- Supports up to 4MP
- Built-in standard PoE (IEEE 802.3af)
- Adaptive IR LEDs reduce IR saturation
- IR Range: 98' (depending on scene reflection)
- True Day/Night operation (IR cut filter)
- IP67 compliant, weather resistant
- IK10 compliant, vandal resistant
- UL listed
- Junction box included
- Conformant with ONVIF profile S
- 5 year warranty*



Included Junction Box



Camera Specifications

Image Sensor	Progressive scan 1/3" CMOS, 4MP
Maximum Resolution	2560(H) x 1440(V)
Minimum Illumination	F2.0, Color: 0.50 lux, BW: 0 lux
Field of View (H)	101°
IR Range	98' (depending on scene reflection)
White Balance	Auto, Manual, Natural, Street Lamp, Outdoor
Exposure Control	Yes
Digital Slow Shutter	Yes
Compensation	BLC / HLC / DWDR
Day/Night	IR cut filter
DNR	3D

Video Specifications

Main Resolution	2560x1440 @ 20fps / 2304x1296 / 1920x1080 / 1280x720 @ 30fps
Compression	H.265, H.264, MJPEG
Bitrate Control	VBR, CBR
Multiple Streaming	2 streams

Network Specifications

Protocols	IPv4/IPv6, TCP, UDP, RTP, RTSP, HTTP, HTTPS, SMTP, FTP, DHCP, DNS
DDNS Support	Speco DDNS (free of charge)
Security	User ID & Password protection, IP address filtering, digest authentication, user access log, HTTPS
User Access	20 users max. Number of simultaneous users may vary depending on resolution

Client Specifications

Web Browser Support	Windows (Internet Explorer 8 and up, Chrome, Firefox)
PC Application	SecureGuard® VMS
Mobile	SecureGuard® Client (iPhone® and Android™)

External Terminal Specifications

Ethernet	10/100 Mbps
Power	DC jack

Other Specifications

Events	Motion detection (4 regions), tamper detection, scene changing, video loss, IP conflict
Alarm Events	Email, record, snapshot
Video Buffer	Configurable pre-record & post-record
Image Settings	Privacy mask, corridor mode

Operating & Unit Specifications

Power	PoE, 12VDC (power supply not included)
PoE	Standard (IEEE 802.3af)
Power Consumption	4W(max)
Operating Temperature	-20°F - 140°F
Operating Humidity	0% - 95% RH
Unit Dimensions	3.86" (H) x 4.8" (Dia.)
Unit Weight	1 lbs.
Certifications	FCC, RoHS
Included in Package	Unit, CD (manual, software), mounting screws, L wrench

Optional Accessories



DSS1
Dome
Sun Shield



O3PMT
Pole Mount
(use with O2VLWM)



NLGPLMT
Pole Mount



NLGCRMT
Corner Mount



O2VLWM
Dome Wall
Mount



POEINJ
12.95W
PoE Injector



PSW5
12VDC
Power Supply

* Effective on all new purchases as of 2/1/17. Visit specotech.com for latest ONVIF® support. ONVIF is a trademark of Onvif, Inc. iPhone and iPad are trademarks of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google Inc. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 10/2/19

