

AXIS Q6074 PTZ Network Camera

Indoor PTZ with HDTV 720p and 30x optical zoom

AXIS Q6074 PTZ Network Camera offers HDTV 720p and 30x optical zoom for great overviews and excellent details. This high-performance indoor PTZ camera comes with autotracking 2 with click and track functionality, as well as an orientation aid for active object tracking and quick orientation. With Axis Lightfinder 2.0 the camera delivers low-light images with more saturated colors and sharper images of moving objects. Plus, enhanced security features such as signed firmware and secure boot ensures the integrity and authenticity of the firmware. Furthermore, Axis Zipstream with H.264/ H.265 significantly lowers bandwidth and storage requirements.

- > [HDTV 720p with 30x optical zoom](#)
- > [Axis Lightfinder 2.0](#)
- > [Autotracking 2 and orientation aid](#)
- > [Built-in analytics](#)
- > [TPM, FIPS 140-2 level 2 certified](#)



AXIS Q6074 PTZ Network Camera

Models	AXIS Q6074 60 Hz AXIS Q6074 50 Hz	Basic analytics (not to be compared with third-party analytics): object removed, enter/exit detector, object counter Supported Support for AXIS Camera Application Platform enabling installation of third-party applications, see axis.com/acap
Camera		
Image sensor	1/2.8" progressive scan CMOS	
Lens	4.25-127.5 mm, F1.6-4.2 Horizontal field of view: 63.8°-2.6° (720p) Vertical field of view: 38.0°-1.47° (720p) Autofocus, auto-iris	
Day and night	Automatically removable infrared-cut filter	
Minimum illumination	Color: 0.1 lux at 30 IRE, F1.6 B/W: 0.002 lux at 30 IRE, F1.6 Color: 0.15 lux at 50 IRE, F1.6 B/W: 0.003 lux at 50 IRE, F1.6	
Shutter time	1/11000 s to 1/3 s with 50 Hz 1/11000 s to 1/3 s with 60 Hz	
Pan/Tilt/Zoom	Pan: 360° endless, 0.05°-450°/s Tilt: 180°, 0.05°-450°/s Zoom: 30x optical, 12x digital, total 360x zoom E-flip, 256 preset positions, tour recording (max 10, max duration 16 minutes each), guard tour (max 100), control queue, on-screen directional indicator, orientation aid PTZ, set new pan 0°, adjustable zoom speed, focus recall	
Video		
Video compression	H.264 (MPEG-4 Part 10/AVC) Baseline, Main and High Profiles H.265 (MPEG-H Part 2/HEVC) Main Profile Motion JPEG	
Resolution	HDTV 720p 1280x720 to 320x180	
Frame rate	Up to 50/60 fps (50/60 Hz) in HDTV 720p	
Video streaming	Multiple, individually configurable streams in H.264, H.265 and Motion JPEG Axis Zipstream technology in H.264 and H.265 Controllable frame rate and bandwidth VBR/ABR/MBR H.264/H.265	
Image settings	Manual shutter time, compression, color, brightness, sharpness, white balance, exposure control, exposure zones, fine tuning of behavior at low light, rotation: 0°, 180°, text and image overlay, polygon privacy masks, image freeze on PTZ, automatic defog, backlight compensation, scene profiles Wide Dynamic Range (WDR): Up to 120 dB depending on scene, highlight compensation	
Audio		
Audio streaming	Two-way, full duplex, half-duplex, simplex	
Audio compression	24bit LPCM, AAC-LC 8/16/32/48 kHz, G.711 PCM 8 kHz, G.726 ADPCM 8 kHz, Opus 8/16/48 kHz Configurable bit rate	
Audio input/output	Requires multicable (sold separately) for external microphone or line input, and line output	
Network		
Security	Password protection, IP address filtering, HTTPS ^a encryption, IEEE 802.1x (EAP-TLS) ^a network access control, digest authentication, user access log, centralized certificate management, brute force delay protection, signed firmware, secure boot, protection of cryptographic keys with FIPS 140-2 certified TPM 2.0 module	
Supported protocols	IPv4, IPv6 USGv6, HTTP, HTTPS ^a , SSL/TLS ^a , QoS Layer 3 DiffServ, FTP, SFTP, CIFS/SMB, SMTP, Bonjour, UPnP [®] , SNMP v1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SRTP, TCP, UDP, IGMP, RTPC, ICMP, DHCP, ARP, SOCKS, SSH, NTCIP, LLDP	
System integration		
Application Programming Interface	Open API for software integration, including VAPIX [®] and AXIS Camera Application Platform; specifications at axis.com AXIS Guardian with One-Click Connection ONVIF [®] Profile G, ONVIF [®] Profile S and ONVIF [®] Profile T, specification at onvif.org	
Analytics	Included AXIS Video Motion Detection, AXIS Motion Guard, AXIS Fence Guard, AXIS Loitering Guard, autotracking 2, active gatekeeper, audio detection	
Event conditions	Audio: audio detection Device status: above operating temperature, above or below operating temperature, below operating temperature, fan failure, IP address removed, network lost, new IP address, shock detected, storage failure, system ready, within operating temperature Edge storage: recording ongoing, storage disruption I/O: digital input, manual trigger, virtual input PTZ: PTZ malfunctioning, PTZ movement, PTZ preset position reached, PTZ ready Scheduled and recurring: scheduled event Video: live stream open	
Event actions	Day/night mode, overlay text, video recording to edge storage, pre- and post-alarm video buffering, send SNMP trap PTZ: PTZ preset, start/stop guard tour File upload via FTP, SFTP, HTTP, HTTPS network share and email Notification via email, HTTP, HTTPS and TCP External output activation, audio recording to edge storage, play audio clip	
Data streaming	Event data	
Built-in installation aids	Pixel counter, leveling guide	
General		
Casing	IP52-rated Metal casing (aluminum), Acrylic (PMMA) clear dome	
Sustainability	PVC free	
Memory	1024 MB RAM, 512 MB Flash	
Power	Axis PoE+ midspan 1-port: 100-240 V AC, max 22.4 W IEEE 802.3at Type 2 Class 4 Camera PoE consumption: typical 11 W, max 17.1 W Multiconnector: 24 V DC +/- 10%, typical 10.5 W, max 16.1 W 24 V AC +/- 10%, typical 16.5 VA, max 25.3 VA	
Connectors	RJ45 10BASE-T/100BASE-TX PoE, multiconnector (cable sold separately) for AC/DC power, 4 configurable alarm inputs/outputs, mic in, line mono input, line mono output to active speaker	
Storage	Support for SD/SDHC/SDXC card Support for SD card encryption Support for recording to network-attached storage (NAS) For SD card and NAS recommendations see axis.com	
Operating conditions	0 °C to 50 °C (32 °F to 122 °F) Humidity 10-85% RH (non-condensing)	
Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F)	
Approvals	EMC EN 55032 Class A, EN 55035, EN 61000-3-2, EN 61000-3-3, EN 61000-6-1, EN 61000-6-2, EN 55024, FCC Part 15 Subpart B Class A, ICES-003 Class A, VCCI Class A, RCM AS/NZS CISPR 32 Class A, KCC KN32 Class A, KN35 Safety IEC/EN/UL 60950-1 IEC/EN 62368-1 Environment IEC/EN 60529 IP52, IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-6, IEC 60068-2-14, IEC 60068-2-27, IEC 60068-2-78 Network NIST SP500-267 Midspan: EN 60950-1, GS, UL, cUL, CE, FCC, VCCI, CB, KCC, UL-AR	
Weight	Camera: 2.85 kg (6.3 lb); with drop-ceiling mount: 3.5 kg (7.7 lb)	
Dimensions	Hard-ceiling: Ø198 x 240 mm (Ø7 13/16 x 9 7/16 in) Drop-ceiling: Ø248 x 243 mm (Ø9 3/4 x 9 9/16 in)	
Included accessories	Axis PoE+ midspan 1-port, Recessed mount for hard and drop ceilings, Smoked dome cover Installation Guide, Windows decoder 1-user license	

Optional accessories	AXIS P55/Q60 Multi-connector cable, 5 m AXIS T91 Mounting Accessories, AXIS T8415 Wireless Installation Tool, AXIS T90 Illuminators, AXIS T8310 Video Surveillance Control Board, multi-user decoder license pack
Video management software	AXIS Companion, AXIS Camera Station, Video management software from Axis' Application Development Partners available on www.axis.com/vms
Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese

Warranty Axis 3-year warranty and AXIS Extended Warranty option, see www.axis.com/warranty

- a. *This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit. (openssl.org), and cryptographic software written by Eric Young (eay@cryptsoft.com).*

Environmental responsibility:

axis.com/environmental-responsibility