

**msi**®

MONITOR
Optix MAG161V
WORK SMART. PLAY HARD.



FEATURE



Portable Design

Extremely light portable monitor which only weights 0.9 kg. You can enjoy the dual-monitor experience not only in work place or at home.



Ultra Slim

The slimmest portable monitor in world. This design allows you easily bring it everywhere.



1920 X 1080

FHD Resolution

With full HD resolution, you can see every details.



Type C Display


Allowing you to connect the latest devices more easily via USB Type C



Mini HDMI

Allowing you to connect all of the devices easily.

CONNECTIONS



1. Power Button

2. Controller

3. 1x Earphone out

4. 1x mini HDMI

5. 1x USB Type C

6. 1x USB Type C

SPECIFICATION

Panel Size	15.6" (40 cm)
Panel Resolution	1920 x 1080 (FHD)
Refresh Rate	60Hz
Panel Type	IPS
Brightness (nits)	180
Viewing Angle	178°(H)/178°(V)
Aspect Ratio	16:9
Curvature	Flat
Contrast Ratio	800:1
DCR	100000000:1
Active Display Area (mm)	344.16(H) x193.59(V)
Pixel Pitch (H x V)	0.17925(H)X0.17925(V)
Surface Treatment	Anti-glare
Display Colors	16.7M
Audio ports	1x Earphone out
Power Type	External USB power
Signal Frequency	147 to 148KHz(H) 47 to 60Hz(V)
Dimension (W x H x D)	357 x 11 x 227 mm, 14.05 x 0.43 x 8.94 inch
Weight (NW / GW)	0.895 kg / 2.645 kg ; 2 lbs / 5.83 lbs
Frameless Design	YES