



[DOWNLOAD SPECS](#)

imagePROGRAF PRO-6100

Printer

Printer Type 11-Colour plus Chroma Optimizer 60-inch Printer

Number of Nozzles Total: 18,432
All colours: 1,536 nozzles

Nozzle Pitch 600 dpi x 2
Non-firing nozzle detection and compensation

Print Resolution (Up to) 2400×1200dpi (Max)

OS Compatibility 2400×1200dpi (Max)
32bit: Windows® (Vista/7/8, 8.1/10)
64bit: Windows 7, Windows 8.1, Windows 10
Windows Server 2008R2 , Windows Server 2012/2012R2
Windows Server 2016 , Windows Server 2019
Mac (OS X 10.10.5 ~ OS10.11), (OS 10.12 ~ macOS 10.14)

Standard Interface USB 2.0 High-Speed
10/100/1000 Base-T/TX
Wireless LAN (IEEE 802.11 b/g/n)
USB Thumb Drive

Ink Droplet Size minimum 4 picoliter

Ink Capacity 160, 330, or 700ml per colour*

Colour Set	Photo Black, Matte Black, Cyan, Magenta, Yellow, Photo Cyan, Photo Magenta, Gray, Photo Gray, Red, I +Chroma Optimizer
Hard Drive	500GB
Media Width	Cut Sheet - 8"- 60" Roll Feed - 8" - 60"
Media Thickness	Roll: 0.07 - 0.8 mm (2.8 - 31.5mil)
Maximum Roll Print Length	Roll Feed - 59' (18 meters)**
Maximum Media Roll Diameter	6.7" (170mm)
Borderless Printing Width (Roll Media Only)	All sizes
Paper-Feed Method	Roll Feed: Two Roll, Front-loading, Front Output Manual Feed: Front-loading, Front Output
Languages	Language: Swift Graphic Raster (SGRaster)
Noise Level (Approx.)	Operation: 50 dB (A) or less Acoustic Power: 6.7 Bels or less
Physical Dimensions	46.0" (H) x 78.7" (W) x 38.7" (D) (with basket open)
Weight	approx.368 lbs (roll holder included, no inks, no print heads)
Power Source	AC 100-240V (50-60Hz)
Power Consumption	Maximum: 103 W or less Standby 3.6 W or less Power Off: 0.3 W or less
Operating Environment	Temperature: 59 - 86°F Relative Humidity: 10-80% (No Condensation)
User-replaceable items	Print Head (PF-10) Maintenance Cartridge (MC-30) Ink Tanks (PFI-1100/PFI-1300/PFI-1700)
Software Included	imagePROGRAF Printer Driver, Professional Print & Layout, Quick Utility Toolbox, Print Plug-In for Office Accounting Manager, Device Management Console, Media Configuration Tool, Printer Driver Extra Kit (Free Layout and Advanced Preview), Print Plug-in for Microsoft Word/Excel/PowerPoint (PC only),

