

# HDMI over CAT6 Extender - 4K 60Hz - 330 ft. (100 m)

Product ID: ST121HD20L



This HDMI® over CAT6 extender lets you transmit your HDMI signal over a CAT6 cable up to 330 ft. (100 m) away. The extender supports Ultra HD 4K with support for 3D and the accompanying digital audio.

## Long-Distance Transmission

Extend your HDMI signal to up to 330 ft. (100 m) with this HDMI over Ethernet extender. Use your existing CAT6 cable infrastructure with a direct connection to the converter for an easy run through walls and ceilings, saving you on installation costs.

The extender also works to extend an infrared (IR) signal, enabling you to control your video source from the remote location.

## Astonishing 4K Picture Quality

This HDMI Ethernet extender supports a 4K 60Hz (3840 x 2160) UHD resolution, providing four times the picture quality of high-definition (1080p), ensuring a crystal-clear picture that's ideal for displaying your 4K video content in office buildings, airports, retail settings and more.

Plus, because the extender supports 1080p and lower resolutions at up to 460 feet away, you can comfortably use this extender to make any video source look great.

## Compatible with HDCP 2.2 Devices

Connect your HDMI devices and displays with confidence, knowing this extender is HDCP 2.2 compliant. This lets you harness the capabilities of HDMI-enabled devices such as Blu-ray players or online streaming devices in higher resolutions. It is also backward compatible with previous generations of HDMI and HDCP.

ST121HD20L is backed by 2-year StarTech.com warranty with free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Extend your 4K HDMI signal in offices, building lobbies, shopping centers, airports and more
- Optimize placement of your demo stations at tradeshow and in auditoriums
- Use existing CAT6 infrastructure to create digital signage

### Features

- Maintains astonishing picture quality up to 330 ft. (100 m) away, with support for UltraHD 4K over non-proprietary CAT6 cabling
- Also supports HD 1080p video resolutions at distances up to 460 ft. (140 m)
- Hassle-free, professional installation with included mounting brackets
- Supports all known HDMI audio formats including Dolby True HD, Dolby Digital and DTS-HD
- Ensured compatibility with HDCP 1.4 / 2.2

<b>Hardware</b>	Warranty	2 Years
	Audio	Yes
	AV Input	HDMI
	AV Output	HDMI
	Cabling	Cat 6 UTP
	Chipset ID	Norelsys NS 5730, NS5731
<b>Performance</b>	Audio Specifications	7.1 Surround Sound
	Max Distance	140 m / 460 ft
	Supported Resolutions	3840x2160 (4K) 60Hz 2560x1600 60Hz 1920x1200 60Hz 1920x1080 (1080p) 60Hz 1280x720 (720p) 60Hz
	Wide Screen Supported	Yes
<b>Connector(s)</b>	Connector A	1 - HDMI (19 pin) Female 1 - RJ-45 Female
	Connector B	1 - HDMI (19 pin) Female 1 - RJ-45 Female
	LED Indicators	2 - Power LED 2 - Link LED
	<b>Power</b>	Input Voltage
Output Current		2
Output Voltage		5V DC
Plug Type		M
Power Source		2 AC Adapters Included
<b>Environmental</b>	Humidity	0% - 95 % RH (No Condensation)
	Operating Temperature	-5°C to 40°C (23°F to 104°F)
	Storage Temperature	-15°C to 55°C (5°F to 131°F)
<b>Physical Characteristics</b>	Color	Black
	Material	Metal
	Product Height	26.000

	Product Length	3 in [7.6 cm]
	Product Width	111.000
	Weight of Product	271.000
<b>Packaging Information</b>	Package Height	95.000
	Package Length	195.000
	Package Width	248.000
	Shipping (Package) Weight	1424.000
<b>What's in the Box</b>	Included in Package	1 - HDMI Transmitter
		1 - HDMI Receiver
		1 - CAT6 Cable
		1 - IR Kit
		2 - Universal Power Adapters (NA/JP, EU, UK, ANZ)
		2 - 3.5 mm to DB-9 RS-232 Adapters
		4 - Mounting Brackets
	1 - Quick-Start Guide	

Product appearance and specifications are subject to change without notice.