



msi

MONITOR
OPTIX MAG272CRX



SPECIFICATIONS

DCI-P3 / sRGB	89% / 113%
Panel Size	27" (69cm)
Aspect ratio	16:9
Panel Resolution	1920 x 1080 (FHD)
Pixel Pitch (H x V)	0.3114(H) x 0.3114(V)
Refresh Rate	240Hz
Response time	1ms
Viewing angle	178° (H) / 178° (V)
Curved	1500R
Brightness	300 nits
Contrast Ratio	3000:1
Power consumption	45W
Control	5-way OSD navigation joystick
Dimension (W x H x D)	611.5 x 560 x 267mm / 24.07 x 22.47 x 10.51 inch
Frameless Design	770 x 595 x 183 mm / 30.3 x 23.43 x 8.4 inch
Weight	Yes
DCR	5.9kg / 13.1 kg
Active Display Area (mm)	13lbs / 28.88lbs
Surface Treatment	100000000:1
Display Colors	597.888 (H) x 336.312 (V)
Video ports	Anti-glare
USB ports	10.7B (8bits + FRC)
Audio ports	1x DP (1.2a)
Kensington Lock	2x HDMI (2.0b)
VESA Mounting	1x USB Type C (DisplayPort Alternate)
Power Type	2x USB 3.2 Gen 1 Type A
Power Input	1x USB 3.2 Gen 1 Type B
Signal Frequency	1x Earphone out
Adjustment (Tilt)	Yes
Adjustment (Height)	100 x 100 mm
Note	Internal Adaptor
Panel Type	100~240V, 50~60Hz
	249.1 to 263KHz (H)
	48 to 240Hz (V)
	-5° ~ 20°
	0 ~ 130mm
	Display Port: 1920 x 1080 (Up to 240Hz)
	HDMI: 1920 x 1080 (Up to 240Hz)
	Type C: 1920 x 1080 (Up to 240Hz)
	VA

FEATURES

- Curved Gaming display (1500R) - The best gameplay immersion.
- Mystic Light - The ultimate gaming finish.
- 240Hz High Refresh Rate - Real smooth gaming.
- 1ms Response Time - eliminate screen tearing and choppy frame rates.
- Gaming OSD App - Create the ultimate viewing settings for your game.
- HDR Ready-Provide eye-catching detail through contrast and shadows adjustment.
- Night Vision: See every detail clearly in the dark, helping you find and attack enemies before they notice.
- Connect with Type-C:Easily connect your laptop or PC to the MSI Optix MAG272CRX display via type-C port.
- AMD FreeSync - prevent screen tearing.
- Anti-Flicker and Less Blue Light - game even longer and prevent eye strain and fatigue.
- Frameless design - Ultimate gameplay experience.
- 178° wide view angle.

