

VGA to RCA and S-Video Converter - USB Power

Product ID: VGA2VID2



This VGA to RCA/S-Video converter box provides a simple way to convert and scale a 1080p VGA video input signal to a 480i composite (CVBS) or S-Video output signal. Perfect for use with legacy projectors or TV sets.

Hassle-Free Setup and Easy to Use

Equipped with a NTSC/PAL toggle switch and a scan button for simple configuration and selection of your video output settings, this compact VGA to Composite and S-Video adapter installs quickly and easily, for a true plug-and-play experience.

Save on Upgrade Costs

By using this VGA to AV adapter you can connect a PC's VGA connector to legacy TVs and projectors, ultimately saving the costs of upgrading your equipment. It's ideal for boardroom settings, medical imaging and watching videos on your S-Video or Composite display.

Crystal-Clear Picture Quality

The PC to television converter features an integrated video scaler circuit that dynamically converts VGA video input signals with resolutions up to 1920x1200 @ 60Hz. To ensure compatibility with your display or projector the computer to TV converter outputs high quality 720 x 480 video, the highest supported by S-Video or Composite.

VGA2VID2 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Great for boardroom meetings, tradeshow, lectures, and CRT digital signage solutions
- An inexpensive way to increase the size of a computer display
- Displays computer screen images on your TV or Projector

Features

- Provides output in both Composite and S-Video formats
- Supports PC input resolutions up to 1920 x 1080
- Select between NTSC and PAL outputs
- Dynamically adjust image underscan and overscan
- Powered by USB port

Hardware	Warranty	2 Years
	Active or Passive Adapter	Active
	Audio	No
	AV Input	VGA
	AV Output	Composite S-Video
Performance	Supported Resolutions	Input - Up to 1920x1080 60Hz Output - 640x480 60Hz
Connector(s)	Connector A	1 - VGA (15 pin, High Density D-Sub) Female Input
	Connector B	1 - S-Video (4 pin, Mini-DIN) Female Output 1 - Composite Video (1 x RCA) Female Output
Power	Plug Type	USB Mini-B (5 pin)
	Power Consumption (In Watts)	2.5W
	Power Source	USB-Powered
Environmental	Humidity	5 to 90 % RH
	Operating Temperature	0 to 50°C (32 - 122°F)
	Storage Temperature	-10 to 80°C (14 to 176°F)
Physical Characteristics	Color	Black
	Product Height	20.000
	Product Length	2.4 in [6 cm]
	Product Width	54.000
	Weight of Product	35.000
Packaging Information	Package Height	24.000
	Package Length	105.000
	Package Width	133.000
	Shipping (Package) Weight	40.000
What's in the Box	Included in Package	1 - VGA to S-Video and Composite Adapter 1 - Mini USB Power Cable 1 - Quick-Start Guide

Product appearance and specifications are subject to change without notice.