



## STYLE, COMFORT AND AUDIO QUALITY.

### **BENEFITS**

- Features great audio and a modern design—so workers want to wear it
- Best-in-class voice quality and a customized fit, the fully adjustable headset has 180-degree pivoting speakers and a flexible microphone boom
- Supports long-wearing comfort with a comfortable, padded headband and pillow soft ear cushions
- Microsoft Teams version to support an easy collaboration and communication with a dedicated Team button for instant access to the Teams App

### **BLACKWIRE 3300 SERIES**

Blackwire 3300 Series provide a best-in-class audio experience in a headset built for enterprise deployment. Even better, workers want to wear it—so your investment pays off. The great appeal of the Blackwire 3300 Series is apparent at first sight: It has a modern, stylish design. Its microphone boom is flexible so workers can customize the fit. And the headset is fully adjustable with a comfort padded headband, pillow soft ear cushions, and 180-degree pivoting speakers. Not only that, it sounds as good as it looks—with high-quality audio you'd expect from Poly. And if it's starting to sound expensive, we've got good news. Blackwire 3300 Series is priced to fit your budget.

- Mono or stereo OTH (over-the-head) options
- Choose the variant for your device: PC USB-A or USB-C and/or 3.5 mm for mobile connectivity
- Corded simplicity and reliability
- Easy to use: no training necessary

## SPECIFICATIONS

### CONNECTS TO

- PC via USB/USB-C, connects to mobile devices and tablets via 3.5 mm (BW3315/BW3325) and devices that support USB-C

### COMPATIBLE WITH

- Windows® or Mac OS

### PC AUDIO RECEIVE FREQUENCY RESPONSE

- Dynamic EQ optimized for PC wideband voice telephony up to 6.8 kHz or for multimedia 20 Hz to 20 KHz (Hi-Fi Stereo BW3320/BW3325)

### SPEAKER SENSITIVITY

- 94 dBSPL ± 4 dB

### SPEAKER IMPEDANCE

- 32 ohm

### SPEAKER SENSITIVITY

- 94 dBSPL + 4 dB

### SPEAKER IMPEDANCE

- 32 OHM

### SPEAKER SIZE

- 32 mm

### HEARING PROTECTION

- SoundGuard: Acoustic limiting for protection against sounds above 118 dBA. G616 support limits the level to 102 dBSPL

### MICROPHONE AND TECHNOLOGY

- Flexible noise canceling microphone

### MICROPHONE FREQUENCY RESPONSE

- 100 Hz to 10 kHz optimized for PC wideband audio up to 6.8 kHz

### MICROPHONE SENSITIVITY

- -38 dBV/Pa ± 4 dB

### WEIGHT

- **Stereo:** 130 g/4.59 oz including inline control, 96 g/3.39 oz headset only
- **Monaural:** 102 g/3.60 oz including inline control, 70 g/2.47 oz headset only

### CALL CONTROLS

- **BW33xx:** Call answer/end button, volume, mute
- **BW33xx-M:** Combined call answer/end and dedicated Microsoft Teams Button, volume, mute

### TONE ALERTS

- Tone alerts for mute on/off and volume maximum/minimum

### WORLDWIDE LIMITED WARRANTY

- 2 year warranty

### APPLICATIONS SUPPORTED

- Plantronics Hub desktop version only, available for Windows/Mac. Plantronics Manager Pro suites: Asset Management and Adoption, Call Quality and Analytics, Health and Safety

## LEARN MORE

For more information on Blackwire 3300 visit [poly.com/Blackwire-3300](https://poly.com/Blackwire-3300)

