

OVERVIEW

Basic rPDUs deliver reliable power to critical IT equipment within a rack or cabinet.

Benefits

- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



Part #: 11011VH

Model Number: XPR120-103D20TL5

Category: Basic

Sub Category: Standard

Power Configuration: 30A, 120V, 2.8kW

Physical Configuration: 19in / 483mm, Horizontal

Product Summary: rPDU, Basic Standard, 30A, 120V, 2.8kW, Horizontal, (12) NEMA 5-20R, 10ft power cord with L5-30P, Black Powder Coat.

Plug Form:



L5-30P

Receptacle:



NEMA 5-20R
(Quantity: 12)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Quantity Of Inputs	1
Voltage	100-120V
Current	30A
VA per Input (Load Capacity)	2.8kW (120V)
Frequency	50/60Hz
Over Current Protection	(2) 20A Single Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	10/3
Power Cable Length	10ft
Plug Type	NEMA L5-30P Twistlock
Receptacle/Socket Type #1	NEMA 5-20R
- Quantity on Face	2
- Quantity on Rear	10
- Quantity per Breaker	6
- Style	Duplex
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	120V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	19in / 483mm Horizontal Rackmount
Adjustable Mount Brackets	Yes
Country of Origin	USA, TAA Compliant and Buy American Act COTS Compliant
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 6.50in
Shipped Weight	8lbs (3.63kg)