

## OVERVIEW

Basic rPDUs deliver reliable power to critical IT equipment within a rack or cabinet.

### Benefits

- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



## Part #: 11013VH

**Model Number:** XPB308-103IN6TL21

**Category:** Basic

**Sub Category:** Standard

**Power Configuration:** 30A, 120/208V WYE, 8.6kW

**Physical Configuration:** 66in / 1683mm, Vertical

### Product Summary:

11013VH - rPDU, Basic Standard, 30A, 120/208V WYE, 8.6kW, Vertical, (24) IEC C13, (6) IEC C19, 10ft power cord with L21-30P, Black Powder Coat.

### Plug Form:



L21-30P

### Receptacle:



IEC C13  
(Quantity: 24)



IEC C19  
(Quantity: 6)

### Chassis Color Options:



To discuss color options, contact your local sales representative.

## Product Specification and Options

### System Features

Quantity Of Inputs	1
Voltage	100-120/200-240V WYE
Current	30A x 3 Phase WYE
VA per Input (Load Capacity)	8.6kW (208V)
Frequency	50/60Hz

<b>Over Current Protection</b>	(3) 20A Double Pole Magnetic Breakers
<b>Switch</b>	Breaker/Switch Combination
<b>Power Cable Wire Gauge</b>	10/5
<b>Power Cable Length</b>	10ft
<b>Plug Type</b>	NEMA L21-30P Twistlock
<b>Combined Total Receptacle/Socket Quantity</b>	30
<b>Receptacle/Socket Type #1</b>	IEC C13
- Quantity on Face	24
- Quantity per Breaker and Phase Combination	8
- Style	Banks of 4
- Maximum Output per Receptacle/Socket	15A per receptacle bank
- Voltage per Receptacle/Socket	208V
<b>Receptacle/Socket Type #2</b>	IEC C19
- Quantity on Face	6
- Quantity per Breaker and Phase Combination	2
- Style	Individual
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	208V
<b>Continuous Operating Temperature Range</b>	10-45C / 50-113F
<b>Heavy Steel - Powder Coat Finish</b>	Black
<b>Configuration</b>	66in / 1683mm Vertical Rackmount
<b>7938 Vertical Mounting Bracket Kit</b>	Yes
<b>Toolless Mounting Hardware - Center to Center Spacing</b>	61.25in and 64.75in
<b>Country of Origin</b>	USA, TAA Compliant
<b>Product Warranty</b>	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
<b>Certification/Agency Approvals</b>	RoHS Compliant
<b>Certification/Agency Approvals</b>	UL & c-UL Listed 60950
<b>Chassis Dimensions (LxWxD)</b>	66.25in x 2.0in x 2.0in
<b>Doghouse (D)</b>	1.44in
<b>Shipped Weight</b>	17lbs (7.71kg)