

OVERVIEW

Basic surge protected rPDUs deliver reliable power to critical IT equipment within a rack or cabinet and comes equipped with built-in surge protection.

Benefits

- Ideal for environments lacking facility-level surge suppression or for applications requiring additional protection.
- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



Part #: 11045VH

Model Number: VSSLN084-101S15

Category: Basic

Sub Category: Surge

Power Configuration: 15A, 120V, 1.4kW

Physical Configuration: 17in / 432mm, Horizontal/Vertical

Product Summary: rPDU, Basic Surge, 15A, 120V, 1.4kW, Horizontal/Vertical, (8) NEMA 5-15R, 10ft power cord with 5-15P, Black Powder Coat.

Plug Form:



5-15P

Receptacle:



NEMA 5-15R
(Quantity: 8)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Quantity Of Inputs	1
Voltage	100-120V
Current	15A
VA per Input (Load Capacity)	1.4kW (120V)

Frequency	50/60Hz
Over Current Protection	15A Thermal Breaker
Switch	No
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	14/3
Power Cable Length	10ft
Plug Type	NEMA 5-15P
Receptacle/Socket Type #1	NEMA 5-15R
- Quantity on Face	8
- Quantity per Breaker	8
- Style	Individual - In-Line
- Maximum Output per Receptacle/Socket	15A
- Voltage per Receptacle/Socket	120V
Center to Center Receptacle Spacing	1.25
Joule Rating	720
Maximum Clamping Voltage	340V
Response Time	< 5 nanoseconds
Technology Used	Super MOVs
Surge Indicator Red LED	Yes
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	17in / 432mm Vertical/Horizontal Rackmount
19in Panel Mount Brackets	Yes
Plastic Mounting Clips	1 - Bottom; 1 - Top
Country of Origin	USA, TAA Compliant and Buy American Act COTS Compliant
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Connected Equipment Warranty	5 years / \$5,000
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	17.00in x 1.61in x 1.61in
Shipped Weight	4lbs (1.81kg)