

OVERVIEW

Metered rPDUs deliver reliable power to critical IT equipment within a rack or cabinet. Includes a local LED display to view real-time power data.

Benefits

- Avoid accidental overloads when deploying or moving critical server equipment with instant access to power consumption metrics on the local digital display.
- The local LED display provides real-time power data for instant feedback when deploying or moving critical IT equipment.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



Part #: 29061VH

Model Number: BRCN100-1025

Category: Metered

Sub Category: Standard

Power Configuration: 20A, 120V, 1.9kW

Physical Configuration: 19in / 483mm, Horizontal

Product Summary:

rPDU, Metered Standard, 20A, 120V, 1.9kW, Horizontal, (10) NEMA 5-20R, 10ft power cord with 5-20P, Black Powder Coat.

Monitoring:

Power - Local (A, V, W, PF)

Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input

Plug Form:



5-20P

Receptacle:



NEMA 5-20R
(Quantity: 10)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	100-120V
Current	20A
VA per Input (Load Capacity)	1.9kW (120V)
Frequency	50/60Hz
Over Current Protection	20A Thermal Breaker
Switch	No
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA 5-20P
Receptacle/Socket Type #1	NEMA 5-20R
- Quantity on Rear	10
- Quantity per Breaker	10
- Style	Duplex
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	120V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	19in / 483mm Horizontal Rackmount
Flush Mount	Yes
Country of Origin	USA, TAA Compliant
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 4.50in
Shipped Weight	8lbs (3.63kg)