

# Lenovo V15 IIL 82C500G5UK

**Product**

Lenovo V15 IIL

**Region**

WE

**Country/Region**

UK Group

**Machine Type**

82C5

**TopSeller**

TopSeller

**Processor**

Intel Core i3-1005G1 (2C / 4T, 1.2 / 3.4GHz, 4MB)

**Graphics**

Integrated Intel UHD Graphics

**Chipset**

Intel SoC Platform

**Memory**

4GB Soldered DDR4-2666 + 4GB SO-DIMM DDR4-2666

**Storage**

256GB SSD M.2 2242 PCIe NVMe 3.0x2

**Display**

15.6" FHD (1920x1080) TN 220nits Anti-glare

**Touchscreen**

None

**Optical**

None

**Media Reader**

4-in-1 Card Reader

**Ethernet**

None

**WLAN + Bluetooth**

11ac, 1x1 + BT4.2

**Case Material**

PC / ABS

**Camera**

0.3MP

**Microphone**

Mono

**Color**

Iron Grey, Texture

**Keyboard**

Non-backlit, English (UK)

**Fingerprint Reader**

None

**TPM**

FW TPM 2.0

**Battery**

Integrated 35Wh

**Power Adapter**

65W Round Tip

**Operating System**

Windows 10 Home 64, English

**Bundled Software**

Office Trial

**Base Warranty**

1-year, Depot

**Bundled Service**

None

**EAN / UPC / JAN**

194778007870

**End of Support**

2026-01-16

**Announce Date**

2019-12-16

 [WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

# Lenovo V15 IIL Platform Specifications

Product Specifications Reference (PSREF)

Processor	10th Generation Intel® Core™ i3 / i5 / i7 Processor								Media reader Ports	4-in-1 reader (MMC, SD, SDHC, SDXC) One USB 2.0, two USB 3.1 Gen 1, HDMI 1.4b, 4-in-1 reader (MMC, SD, SDHC, SDXC), combo audio / microphone jack, AC power adapter jack <i>* Depending on many factors, actual data transfer speed may be lower than theoretical speed.</i>
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics		
	i3-1005G1	2	4	1.2 GHz	3.4 GHz	4MB	DDR4-2666	Intel UHD Graphics		
	i5-1035G1	4	8	1.0 GHz	3.6 GHz	6MB		Intel Iris® Plus Graphics		
	i5-1035G4			1.1 GHz	3.7 GHz	8MB				
i7-1065G7	1.3 GHz			3.9 GHz						
Graphics	Intel UHD Graphics or Intel Iris Plus Graphics in processor only, or Intel UHD Graphics or Intel Iris Plus Graphics in processor and NVIDIA® GeForce® MX330, 2GB GDDR5 memory; supports external digital monitor via HDMI; supports dual independent display; Max resolution: 4096x2304@24Hz (HDMI)								Camera Audio support	0.3MP, fixed focus, with monaural microphone HD Audio, Dolby Audio™, stereo speakers, 1.5W x 2, monaural microphone, combo audio / microphone jack
Chipset Memory	Intel SoC (System on Chip) platform 12GB max / 2666MHz DDR4, 4GB memory soldered to systemboard, one DDR4 SO-DIMM socket								Keyboard Touchpad	6-row, spill-resistant, multimedia Fn keys, numeric keypad Buttonless Mylar multi-touch touchpad
Display	<i>One of the following, configurable by model:</i>								Security Security chip Fingerprint reader	Power-on password, hard disk password, supervisor password Firmware TPM 2.0, integrated in chipset None
	<ul style="list-style-type: none"> <li>15.6" (396mm) HD (1366x768), anti-glare, LED backlight, 220 nits, 16:9 aspect ratio</li> <li>15.6" (396mm) FHD (1920x1080), anti-glare, LED backlight, 220 nits, 16:9 aspect ratio</li> </ul>								Battery Max battery life	Integrated Li-Polymer 30Wh or 35Wh battery <i>MobileMark® 2014: 5.5 hr (30Wh) or 6 hr (35Wh)</i> <i>* Battery life varies significantly with settings, usage, &amp; other factors.</i>
Multi-touch	None								AC adapter	65W round tip AC adapter
Storage	<i>Up to 2 drives (one HDD and one M.2 SSD):</i>								Preload (opt)	<i>Preloaded operating system</i> <ul style="list-style-type: none"> <li>Windows® 10 Home 64</li> <li>Windows 10 Pro 64</li> </ul> <i>Preloaded applications (only some listed)</i> <ul style="list-style-type: none"> <li>Microsoft Office Trial (with 30-day license)</li> <li>Microsoft Office 365 Home</li> <li>Microsoft Office 365 Personal</li> <li>Microsoft Office Home and Business 2019</li> <li>Microsoft Office Home and Student 2019</li> <li>Microsoft Office Professional 2019</li> <li>Microsoft Office Personal 2019</li> </ul>
Optical	None									
Ethernet	None									
WLAN + Bluetooth™	<i>One of the following, configurable by model:</i>									
	<ul style="list-style-type: none"> <li>802.11ac 1x1 Wi-Fi + Bluetooth 4.2, M.2 Card</li> <li>802.11ac 2x2 Wi-Fi + Bluetooth 5.0, M.2 Card</li> </ul>									
Dimensions Weight Case color Case material	<i>WxDxH:</i> 14.26" x 9.9" x 0.78"; 362.2mm x 251.5mm x 19.9mm Starting at 4.08 lb / 1.85 kg Iron grey, IMR or Texture PC/ABS plastic								Limited warranty	<i>One of the following, configurable by model:</i>
									Environment	ErP lot3; RoHS-compliant

Note: The specifications above may not be available in all regions.

Lenovo  
May 2020



# Lenovo V15 IIL

