

M15-13M

Compact multifunctional document camera

The new AVer M15-13M may be small in size, but it packs a punch to provide your students with the clearest view of your lesson plan content. Between the 13 megapixel camera and 4K output, the M15-13M brings your lesson material to life. Taking a look at crystal formations or a dismantled owl pellet? The 23X digital zoom almost takes you down to the molecular level.



- 4K**
Output
- 13MP**
Camera
- 23X**
Digital Zoom
- 3Yr**
Warranty

True distance learning solution

Want to stream and share your lessons with other classes and schools live? The high definition resolution with built-in microphone supports integration with Skype or Zoom applications, while the compact design and rotating camera head allows you to place and point the camera anywhere in the room.



Compact design

Fully foldable and collapsible, the M15-13M is perfect for the typical crowded classroom, but also is easily stored and secured. Share between classrooms, or move throughout the classroom, the M15-13M can go anywhere.



Software is as simple as one touch

With our new AVerTouch software, it's never been easier to engage your students with every click! Present real-life content, while enhancing every step of your curriculum with powerful multitasking and editing tools. Then, save your lessons or student projects to the Cloud with one simple touch.



Engaging visuals

Showcase the vivid colors of a flower, or the fine details of a butterfly, the clarity of the M15-13M is sure to engage and captivate your students like it was right on their desk.



Specifications

| | | | | | |
|--------------------------|---|---------------------|----------------------------------|---------------------------|--|
| Sensor | 1/3.06" VCM | Pixel Count | 13 megapixels | | |
| Frame Rate | 60 fps (max.) | Image mode | Normal/ High Frame/ High Quality | Effect | Rotate/ Freeze |
| HDMI Output | 4K; HD 1080p 60Hz; HD 720p 60Hz | Focusing | Auto/ Manual/ Area (SW) | Shooting Area | 426mmx 313mm @ 330 mm |
| Zooming | Total 23X maximum | Dual Mode | N/A | WiFi Streaming | N/A |
| Dual Band | N/A | Miracast | No | Compatibility | N/A |
| Wireless Security | N/A | Power Source | DC5V/ 2A, AC 100-240V | Consumption | 4 Watts (lamp on) 3.5 Watts (lamp off) |
| USB Bus Power | Yes (Standby mode only) | Lamp Type | LED light | USB | Type mini-Bx1 |
| DC 5V Input | Power Jack | MIC | Built-in | Operating | 518mm(L)x 84 mm(W)x 351mm(H) (+/-2mm include rubber foot) |
| Folded | 280mm(L)x 84mm(W)x 42mm(H) (+/-2mm include rubber foot) | Weight | 1.4 kg (about 3.1 lbs) | Software Supported | ePTZ, Image/ Area capture, Picture by picture, Timer, Cloud library, Recording, Annotation |
| Warranty | 3 year warranty All AVerVision Accessories : 1 year warranty (Rechargeable battery: 1 year warranty) | | | | |

Note: Specifications subject to change without notice



Aver Information Inc. Americas averusa.com. 668 Mission Court, Fremont, CA 94539
T:408.263.3828 F:408.263.8132 Toll free:1.877.528.7824

©Copyright 2020, AVer Information Inc. All rights reserved. Specifications subject to change without notice.