



Dell UltraSharp 24 Monitor U2415 24"



Dell UltraSharp 24 Monitor | U2415
61.1 cm (24 inches)


Delivering superior Dell UltraSharp performance for virtually everyone

Enjoy a virtually borderless viewing experience that's perfect for multi-monitor use with the Dell UltraSharp 24 Monitor – U2415.

For More Information visit
www.dell.com/monitors



Dell UltraSharp 24 Monitor | U2415
61.1 cm (24 inches)



Dell UltraSharp 24 Monitor | U2415
61.1 cm (24 inches)

The Dell UltraSharp 24 Monitor offers you:

World class screen performance

View images and documents easily with superb Dell UltraSharp screen clarity and precise color performance on this large, 24" viewing area.

- Enjoy consistent, accurate colors right out of the box — each Dell UltraSharp 24 Monitor is factory tuned at 99% sRGB with a $\Delta E < 3$.
- To enhance collaboration with co-workers, colors on the screen remain consistent from virtually any angle with this monitor's ultra-wide viewing angle.
- Conveniently view two full documents side by side on the large, 16:10 aspect ratio, 24" viewing area with WUXGA 1920 x 1200 resolution.
- Help boost your productivity with a dual or multi-monitor setup and take advantage of the ultra-thin (6.9 mm) bezel that allows virtually borderless viewing between monitors.

Outstanding usability

Enjoy excellent connectivity and flexible viewing options that make the U2415 easy to use.

- Easily pivot 90° clockwise or counter-clockwise placing the thinnest edges side by side for an enhanced screen experience with a multi-monitor set up.
- Work the way you like with the fully adjustable U2415 including tilt, pivot, swivel and height adjustable stand features.
- Connect seamlessly to your PC and other peripherals simultaneously without compromising on picture quality via digital connectivity.
- Display content from your smartphone or tablet directly on the large monitor screen and charge it at the same time when you connect either device via MHL to your U2415 monitor.
- A high current USB 3.0¹ charging port supplies twice the power for charging and powering BC1.2 compatible devices.


Reliability and eco-efficiency

- Minimize downtime and gain peace of mind with:
 - Premium Panel Guarantee² which offers a free panel exchange in the event that you discover even one bright pixel during the Limited Hardware Warranty³ period.
 - Dell's 3-year Limited Hardware Warranty and Advanced Exchange Service⁴, providing you with quality you can count on.
- Made of environmentally preferable materials, the Dell UltraSharp 24 Monitor is designed with more than 25% post consumer recycled materials in its chassis, is BFR/ PVC-free (excluding external cables), arsenic-free glass and a mercury-free LED panel.
- Rest assured that the Dell UltraSharp 24 Monitor meets the latest environmental standards such as ENERGY STAR®, EPEAT® Gold⁵ and TCO Certified Displays.

Perfect for:

- Dual/multi-monitor set up to promote increased productivity
- Displaying legacy applications requiring 16:10 aspect ratio
- Programming and software development
- Office applications

Easily adjust the panel to your preferred viewing position to work the way you like.



Connectivity



- A Power adapter
- B Dell soundbar mounting slots
- C HDMI (MHL)
- D DisplayPort
- E Mini DisplayPort in
- F Mini DisplayPort out
- G Audio-Line out
- H USB upstream
- I USB downstream
- J Stand lock



What's in the box?

Monitor, stand, cable cover, power cable (varies by country), DisplayPort cable (mini-DP to DP), USB 3.0 upstream cable (enables the USB ports on the monitor), drivers and documentation media, quick set up guide, product and safety information guide, Factory Calibration Report.

Dell recommends that customers dispose used computer hardware, including monitors, in an environmentally sound manner. Potential methods include reuse of parts or whole products and recycling of product, components and/or materials. For more information, please visit http://dell.com/recycling_programs and www.dell.com/environment



Dell UltraSharp 24 Monitor | U2415

Display

Model number	U2415
Viewable image size (diagonal)	61.1 cm (24.1 inches)
Active display area	
Horizontal	518.40 mm (20.41 inches)
Vertical	324.00 mm (12.75 inches)
Maximum resolution	WUXGA 1920 x 1200 at 60 Hz
Aspect ratio	16:10
Pixel pitch	0.27 mm x 0.27 mm
Brightness (typical)	50 to 300 cd/m ²
Color gamut (typical)	91% ⁶ (CIE1976), 99% sRGB (delta E <3)
Color depth	16.78 million colors
Contrast ratio (typical)	1000:1
Dynamic contrast ratio (max)	2 million:1
Viewing angle (typical) (vertical/horizontal)	178° / 178°
Response time (typical)	Fast mode: 6 ms gray-to-gray (typical) Normal mode: 8 ms gray-to-gray (typical)
Panel technology	In-plane switching, anti-glare with hard coat 3H
Backlight	LED
Speakers (optional)	AC511

Connectivity

Connectors	2xHDMI(MHL), 1xMini DisplayPort/ DisplayPort 1.2 ⁷ , 1 DisplayPort out (MST), 1 x Audio Line out, 5 x USB 3.0 ports
------------	--

Design features

Stand	Height-adjustable stand, tilt (typical: 5° forward or 21° backward) , pivot (clockwise and counterclockwise), swivel and built in cable-management
VESA mounting support (wall mount kit sold separately)	Dell Quick Release feature (100 mm x 100 mm)
Security	Security lock slot (security lock not included)

Power

AC input voltage/frequency/current	100 to 240 VAC/50 or 60 Hz ± 3 Hz/1.5 A (maximum)
Power consumption (typical)	23W
Power consumption standby/sleep mode	<0.5 W

Dimensions (with stand)

Height (compressed ~ extended)	402.9 mm (15.86 inches) ~ 517.9 mm (20.39 inches)
Width	532.2 mm (20.95 inches)
Depth	205.0 mm (8.07 inches)

Weight

Weight (panel only – no stand)	4.25 kg (9.35 lb)
Weight (with stand)	6.69 kg (14.72 lb)
Shipping weight	9.00 kg (19.80 lb)

Standard service plan

- 3 Years Advanced Exchange Service⁴ & 3 Years Limited Hardware Warranty³
- Premium Panel Guarantee²

Environmental compliance

ENERGY STAR®, EPEAT® Gold⁵, TCO Certified Displays, China Energy Label, RoHS, WEEE, ErP (EuP) Standards, Korea E-Standby

^{*} Registered in US and Canada only.

¹ For charging BC1.2 devices and also supports up to 2A when powering standard USB devices.

² In the event you discover even one bright pixel during the Limited Hardware Warranty period, a free panel exchange is guaranteed. (see pixel panel info located on Dell.com web page for complete details):

<http://support.dell.com/support/topics/global.aspx/support/kcs/document?docid=414288>

³ For a copy of the Limited Hardware Warranty, write Dell USA LP, Attn: Warranties, One Dell Way, Round Rock, TX 78682 or see dell.com/warranty.

⁴ Advanced Exchange Service: Replacement part/unit dispatched, if needed, following completion of phone/online diagnosis. Fee charged for failure to return defective unit. Availability varies. Other conditions apply.

⁵ EPEAT Gold registered in the U.S. EPEAT registration varies by country. See www.epeat.net for registration status by country.

⁶ Color gamut (typical) is based on CIE1976 (91%) and CIE1931 (76%) test standards.

⁷ DisplayPort 1.2 - Supports High Bit Rate 2 (HBR2) and Multi-stream transport (MST). U2415 does not support fast AUX transaction, 3D stereo transport and HBR (High bit rate) audio.

Based on Ad# A14000385 dell.com/monitors

Product availability varies by country. Please contact your Dell representative for more information.