

3 ft CAT6 Patch Cable - 10 Pack - 100% Copper Wire - Blue

Product ID: C6PATCH3BL10PK



This CAT6 cable pack meets all Category 6 cable specifications, to deliver a reliable Gigabit network connection.

The CAT6 patch cable 10-pack is built using 100% copper wire and is tested to comply with ANSI/TIA 568 C.2 Category 6 requirements. We don't use copper-clad aluminum (CCA) wire, which is subject to problems like weak power delivery, heat buildup, equipment damage and possibly fire.

The 50-micron gold connectors deliver optimum conductivity and eliminate signal loss due to oxidation or corrosion.

The CAT6 Ethernet cords are manufactured using high-quality copper conductors and carefully constructed and tested to keep Near-End Crosstalk (NEXT) well within acceptable limits. The patch cables are built with 24 AWG copper wire, to ensure peak performance for demanding Ethernet applications such as Power-over-Ethernet and 4K or 1080p video streaming.

For trouble-free cable runs, these durable cables feature molded boots which offer strain relief by stopping the RJ45 connectors from bending at sharp angles. This reduces the risk of cable damage, which could decrease network connectivity and performance.

C6PATCH3BL10PK is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Designed for use with Gigabit networks
- Patches from hub to distribution panel

- Connects workstation to wall outlet

Features

- Protect your network and equipment with 100% copper wire CAT6 cables
- Tested to comply with ANSI/TIA 568 C.2 CAT6 requirements
- Molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles
- Built with 50-micron gold-plated connectors for a clear signal
- Convenient solution for businesses in need of multiple CAT6 networking cables

Hardware	Warranty	90 Days
	Number of Conductors	4 Pair UTP
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Fire Rating	CMG Rated (General Purpose)
	Cable Type	Molded
	Wiring Standard	TIA/EIA-568-B.1-2001 T568B
Performance	Cable Rating	CAT6 - 650 MHz
Connector(s)	Connector A	RJ-45
	Connector B	RJ-45
Physical Characteristics	Color	Blue
	Wire Gauge	24 AWG
	Conductor Type	Stranded Copper
	Cable Length	36.0 in [9.1 cm]
	Product Length	36.0 in [9.1 cm]
	Product Width	0.5 in [11.600 mm]
	Product Height	0.3 in [8.200 mm]
	Weight of Product	15.9 oz [450.000 g]
Packaging Information	Package Length	12.9 in [3.3 cm]
	Package Width	10.0 in [2.6 cm]
	Package Height	1.6 in [40.000 mm]
	Shipping (Package) Weight	16.2 oz [460.000 g]
What's in the Box	Included in Package	CAT6 Cables

**Product appearance and specifications are subject to change without notice.*

