

ThinkVision S28u-10 61E6GAR2US

Product

ThinkVision S28u-10

Machine Type

61E6

Region

NA, LA

Display Size

28"

View Area

631.928x359.78 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

3840x2160

Pixel Pitch

0.1617x0.1580 mm

Dot / Pixel Per Inch

157.35 dpi

View Angle (H / V)

178 / 178

Pixel Response Time

4 ms (Extreme mode) / 6 ms (Typical mode) / 14 ms (off mode)

Brightness

300 nits

Contrast Ratio

1000:1

Color Gamut

99% sRGB, 90% DCI-P3

Multiple Input

HDMI, DP

USB Port

None

Camera

None

Speaker

None

Power Consumption (Typical / Maximum)

31W / 48W

Power Adapter

Integrated

Stand

Tilt Stand

Color

Raven Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

450.82x636.94x229.99 mm

Weight (Including Stand)

11.55 lb / 5.24kg

Monitor Cable

HDMI

ENERGY STAR

Yes

TCO

TCO 8.0

EPEAT

Silver

Low Blue Light / Eye Comfort

Eye Comfort

Base Warranty

3-year

Operating System

Support Windows 7, Windows 10

Presets / User Settings

15

On Screen Display

OSD, 8 Languages

Sync Technology

None

CPU / Platform

None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Announce Date

2020-01-11

 WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

ThinkVision S28u-10

DISPLAY

Panel Size

28-inch

Screen Dimensions

631.928 mm x 359.78 mm

Panel Type

3-side NearEdgeless,
In-Plane Switching

Backlight

WLED

Aspect Ratio

16:9

Resolution

3840 x 2160

Refresh Rate

60 Hz

Pixel Pitch (H x V)

0.16 x 0.16

Dot/Pixel Per Inch (DPI/PPI)

157.35

Viewing Angle (H x V @ CR 10:1)

178° / 178°

Response Time

4ms (Extreme Mode)
6ms (Normal Mode)

Brightness (typical)

300 cd/m²

Contrast Ratio (typical)

1000:1

Dynamic Contrast Ratio (typical)

3M:1

Color Gamut

99% sRGB,
90% DCI-P3

Color Support (typical)

1.07 Billion

CONNECTIVITY

Video Input Signals

HDMI 2.0 + DP 1.2

Audio Signal

1 x Audio Out (3.5mm)

POWER

Power Consumption (Typical/Max)

31W / 48W

Power Consumption Sleep/Off Mode

<0.3W

Power Consumption Switch Off-Mode

<0.3W

Power Supply

Internal

Energystar Power Consumption (P_{on}/E_{TEC})

24.28W / 75.41kWh

Voltage Required

AC 90 to 264 V (50/60 Hz)

DIMENSIONS

Size Packed (D x H x W) (mm/inch)

127 x 723 x 452 mm /
5 x 28.46 x 17.80 inches

Size Unpacked w/stand (D x H x W) (mm/inch) (Lowest position)

229.99 x 450.82 x 636.94 mm /
9.05 x 17.72 x 25.08 inches

Size Unpacked w/o stand (D x H x W) (mm/inch) (Highest position)

229.99 x 450.82 x 636.94 mm /
9.05 x 17.72 x 25.08 inches

Size Unpacked w/o stand (D x H x W) (mm/inch) (Head Only)

49.2 x 373.68 x 636.94 mm /
1.94 x 14.71 x 25.08 inches

Weight Packed

7.0 kg / 15.43 lbs.

Weight Unpacked

5.24 kg / 11.55 lbs.

Weight (Monitor Head Only)

4.58 kg / 10.10 lbs.

SPECIAL FEATURES

Anti-glare

Yes

ThinkCentre Tiny Support

Yes

MECHANICAL

Tilt Angle (front/back)

-5° / 22°

VESA Mount Capability

Yes (100 x 100 mm)

Kensington Lock Slot

Yes

Bezel Color

Raven Black

Bezel Width (side)

2.0 mm

Bezel Width (top/bottom)

2.0 / 22.8 mm

WHAT'S IN THE BOX

Monitor with stand
1 x Power cable (1.8 m)
1 x HDMI cable (1.8 m)
Quick setup guide

CERTIFICATIONS

ENERGY STAR Rating

8.0

CCC

Yes

TCO

8.0

TCO Edge

2.0

EPEAT

Silver

RoHS (EU 2002/95/EC)

Yes

Windows Certification

Windows 7, Windows 10

China Energy Efficiency Standard

Tier 1

TÜV Rheinland Eye Comfort

Yes



Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: - 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2020 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

Lenovo

ThinkVision S28u-10

