



# msi

## MONITOR Optix G241



### SPECIFICATION

DCI-P3 / sRGB	95% / 128%
Panel Size	23.8" (60cm)
Aspect ratio	16:9
Panel Resolution	1920 x 1080 (FHD)
Pixel Pitch (H x V)	0.2745(H) x 0.2745(V)
Refresh Rate	144Hz
Response time	1ms
Viewing angle	178° (H) / 178° (V)
Brightness	250 nits
Contrast Ratio	1000:1
Power consumption	25W
Control	5-way OSD navigation joystick
Dimension (W x H x D)	540.3 x 422.6 x 219.6 mm / 21.27 x 16.64 x 8.65 inch 606 x 409 x 172 mm / 23.86 x 16.10 x 6.77 inch
Frameless Design	Yes
Weight	3.3kg / 5.0kg 7.28lbs / 11.02lbs
DCR	100000000:1
Active Display Area (mm)	527.04(H) x 296.46(V)
Surface Treatment	Anti-glare
Display Colors	16.7M
Video ports	1x DP (1.2a) 2x HDMI (1.4b)
Audio ports	1x Earphone out
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Power Type	Internal Adaptor
Power Input	100~240V, 50~60Hz
Signal Frequency	30 to 100KHz (H) 47 to 145KHz (V)
Adjustment (Tilt)	-5° ~ 20°
Note	Display Port: 1920 x 1080 (Up to 144 Hz) HDMI: 1920 x 1080 (Up to 144 Hz) DCI-P3 and sRGB follow CIE1976 Standard
Panel Type	IPS

### FEATURE



#### eSports Gaming

MSI eSports gaming monitor will enhance your competitive gameplay to ensure you are always at your best levels.



#### IPS Panel

Optimize the screen colors and brightness to enhance your viewing experience.

#### 144Hz High Refresh Rate



Experience smooth gaming with a blazing fast 144Hz refresh rate, that gives you the upperhand in fast moving games.

#### 1ms Fast Response Time



Eliminate screen tearing and choppy frame rates with 1ms response time.



#### Wide Color Gamut


Game colors and details will look more realistic and refined, to push game immersion to its limits.

#### Night Vision



See every detail clearly in the dark, helping you find and attack enemies before they notice.

### CONNECTIONS



- 1. 5-way joystick navigator
- 2. 1x DC jack
- 3. 2x HDMI (1.4b)
- 4. 1x Display Port (1.2a)
- 5. 1x Earphone out
- 6. 1x Kensington lock