

**msi**®

MONITOR

**Optix MAG272CQR**

## FEATURE



### Curved Gaming

MSI Curved Gaming Monitor will give you the most immersive and competitive edge you need to take down your opponents.



### WQHD High Resolution

Game titles will even look better, displaying more details due to the WQHD resolution.



### Gaming OSD APP

Customize and set the ultimate monitor modes with keyboard & mouse in a very easy way.



### HDR Ready

Provide eye-catching detail through contrast and shadows adjustment.



### 165Hz High Refresh Rate

Experience smooth gaming with a blazing fast 165Hz refresh rate, that gives you the upperhand in fast moving games



### 1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.

## CONNECTIONS



1. Power Jack	6. 2x USB 3.2 Gen1 Type A
2. 1x Display Port 1.2a	7. 1x USB 3.2 Gen1 Type B (PC to Monitor)
3. 2x HDMI 2.0b	8. 1x Kensington Lock
4. 1x USB Type C (For DP and Charge)	9. Headset Hanger
5. 1x Earphone	

## SPECIFICATION

DCI-P3 / sRGB	90% / 100%
Panel Size	27" (69cm)
Aspect ratio	16:9
Panel Resolution	2560 x 1440 (WQHD)
Pixel Pitch (H x V)	0.2331(H) x 0.2331(V)
Refresh Rate	165Hz
Response time	1ms
Viewing angle	178° (H) / 178° (V)
Curved	1500R
Brightness	300 nits
Contrast Ratio	3000:1
Power consumption	61W
Control	5-way OSD navigation joystick
Dimension (W x H x D)	611.5 x 560 x 267 mm / 24.07 x 22.47 x 10.51 inch 790 x 475 x 214 mm / 31.1 x 18.7 x 8.4 inch
Frameless Design	Yes
Weight	5.9kg / 13.1kg 13lbs / 28.88lbs
DCR	100000000:1
Active Display Area (mm)	596.736(H) x 335.664(V)
Surface Treatment	Anti-glare
Display Colors	10.7B (8bits + 2FRC)
Video ports	1x DP (1.2a) 2x HDMI (2.0b)
USB ports	2x USB 2.0 1x USB 2.0 Type B
Audio ports	1x Earphone out
Kensington Lock	Yes
VESA Mounting	100 x 100 mm
Power Type	Internal Adaptor
Power Input	100-240V, 50-60Hz
Signal Frequency	70.56 to 243.37KHz (H) 48 to 165Hz (V)
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Height)	0 ~ 130mm
Note	Display Port: 2560 x 1440 (Up to 165Hz) HDMI: 2560 x 1440 (Up to 165Hz)
Panel Type	Samsung VA