



Lexmark C3426dw

Productivity. Reliability. Security.



Lexmark C3426dw

Give every small workgroup bold, consistent color output with the compact, lightweight Lexmark C3426dw. Built for reliability, performance and security, it prints up to 26 ppm* and offers expandable input for longer print runs. Take control with a 2.8-inch (7.2 cm) touch screen and connect via Wi-Fi, USB, Ethernet, or the cloud.

Compact color power

- ▶ Get color output at up to 26 pages per minute*.
- ▶ Tackle your printing workload with the power of a 1-GHz dual-core processor and 512 MB of memory.
- ▶ Compact dimensions of 9.6 inches high x 16.2 inches wide x 15.5 inches deep (243.7 mm high x 411.2 mm wide x 394.1 mm deep) help it fit almost anywhere.



Connect and command

- ▶ Connect via Wi-Fi, Gigabit Ethernet, or USB.
- ▶ Simplify mobile printing with the Lexmark Mobile Print app, Google Cloud Print, Mopria®, and AirPrint.
- ▶ Take command of device settings and monitor vital system functions on a 2.8-inch (7.2 cm) color touch screen.
- ▶ Built-in cloud connectors let you securely access files from popular cloud services Box, DropBox, Google Drive, and Microsoft OneDrive.

Sustained output, enduring quality

- ▶ Genuine Unison™ replacement toner offers rich, vibrant color in available Extra High Yield cartridges that provide up to 4,500 pages of output** for more printing and less downtime.
- ▶ Single-piece cartridge simplifies supply replacement for fewer interruptions.
- ▶ Optional input trays increase total input capacity to 751 sheets to support longer print runs and enhanced media flexibility.
- ▶ A steel frame and lifetime imaging components mean long life and minimal maintenance.

Robust, built-in security

- ▶ Lexmark's full-spectrum security architecture helps keep your information safe—in the document, on the device, over the network, and everywhere in between.


Save paper, save energy

- ▶ Automatic two-sided printing is standard.
- ▶ Built-in energy-saving modes help support ratings of EPEAT® Silver and ENERGY STAR® certified.
- ▶ The Lexmark Cartridge Collection Program (LCCP) and Lexmark Equipment Collection Program (LECP) minimize waste and support recycling (availability varies by country).

* Print speeds measured in accordance with ISO/IEC 24734 (ESAT). For more information see: www.lexmark.com/ISOspeeds.

** Average continuous black or continuous composite color (CMY) declared yield in one-sided (simplex) mode up to this number of pages in accordance with ISO/IEC 19798. Actual yield will vary considerably based upon many factors. See www.lexmark.com/yields for more information.

Lexmark C3426dw



- 1 **Printer with 2.8-inch (7.2 cm) touch screen**
9.6 x 16.2 x 15.5 in.
243.7 x 411.2 x 394.1 mm
- 2 **250-Sheet tray**
Dimensions included as part of base model

- 3 **250-Sheet Tray**
4.1 x 16.2 x 15.0 in.
103.9 x 411.2 x 381.0 mm
- 4 **250-Sheet Tray**
4.1 x 16.2 x 15.0 in.
103.9 x 411.2 x 381.0 mm

	Standard
	Optional

Product Specifications		Lexmark C3426dw
Printing		
Display	2.8 inch (7.2 cm) LCD touch panel	
Print Speed	Up to: Black: 26 ppm ¹ (Letter) / Color: 26 ppm ¹ (Letter)	
Time to First Page	As fast as: Black: 10.9 seconds / Color: 11 seconds	
Print Resolution	Black: 4800 Color Quality, 600 x 600 dpi / Color: 600 x 600 dpi, 4800 Color Quality	
Memory	Standard: 512 MB / Maximum: 512 MB	
Hard Disk	Not Available	
Recommended Monthly Page Volume	600 - 2500 pages ²	
Maximum Monthly Duty Cycle	Up to: 50000 pages per month ³	
Supplies ⁴		
Laser Cartridge Yields	up to: 4,500 ⁵ -page Black and Color (CMYK) Extra High Yield Cartridges / up to: 1,500 ⁵ -page Black and Color (CMYK) Cartridges	
Cartridge(s) Shipping with Product	1,500 ⁵ -page Black Return Program Toner Cartridge, 1,500 ⁵ -page color (CMY) Return Program Toner Cartridges	
Paper Handling		
Included Paper Handling	100-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed, 250-Sheet Input	
Paper Input Capacity	Up to: Standard: 250+1 pages 20 lb or 75 gsm bond / Maximum: 250+1 pages 20 lb or 75 gsm bond	
Paper Output Capacity	Up to: Standard: 100 pages 20 lb or 75 gsm bond / Maximum: 100 pages 20 lb or 75 gsm bond	
Media Types Supported	Paper Labels, Card Stock, Plain Paper, Envelopes, Glossy Paper, Refer to the Paper & Specialty Media Guide	
Media Sizes Supported	A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Hagaki Card, Letter, B5 Envelope, Statement, C5 Envelope, Executive, Universal, DL Envelope, Folio, 10 Envelope	
General Information ⁶		
Standard Ports	802.11b/g/n Wireless, USB 2.0 Specification Hi-Speed Certified (Type B), Ethernet 10/100/1000 BaseTX (RJ-45)	
Noise Level	Operating: 51/53 dBA (Print)	
Specified Operating Environment	Humidity: 8 to 80% Relative Humidity / Altitude: 0 - 3048 Meters (10,000 Feet) / Temperature: 10 to 32°C (50 to 90°F)	
Limited Warranty	See Statement of Limited Warranty: 1-Year Advanced Exchange, Next Business Day	
Size / Weight	H x W x D: 9.6 x 16.2 x 15.5 in. / 35.5 lb.	
ENERGY STAR Typical Electricity Consumption	TEC: 0.36 kilowatt-hours per week	

All information is subject to change without notice. Lexmark is not liable for any errors or omissions.

¹ Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: www.lexmark.com/ISOspeeds.

² "Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. ³ "Maximum Monthly Duty Cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. ⁴ Product functions only with replacement cartridges designed for use in a specific geographical region. See www.lexmark.com/regions for more details. ⁵ Average continuous black or continuous composite CMY declared cartridge yield up to this number of standard pages in accordance with ISO/IEC 19798. ⁶ Printers are sold subject to certain license/agreement conditions. See www.lexmark.com/printerlicense for details.

© 2020 Lexmark. All rights reserved.

Lexmark, the Lexmark logo and Unison are trademarks of Lexmark International, Inc., registered in the United States and/or other countries.

Apple and AirPrint are trademarks of Apple Inc., registered in the U.S. and other countries. Google Cloud Print is a trademark of Google, LLC. MOPRIA®, the Mopria® Logo™ and the Mopria® Alliance logos are registered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. ENERGY STAR and the ENERGY STAR mark are registered trademarks owned by the U.S. Environmental Protection Agency. EPEAT® is a trademark of the Green Electronics Council in the United States and other countries. All other trademarks are the property of their respective owners.

This product includes software developed by the OpenSSL Project for use in the Open SSL Toolkit (<http://www.openssl.org/>).

