

15U 19" Open Frame Server Rack - 4 Post Adjustable Depth 23-41" Mobile - Free Standing Rolling Network/Computer Equipment Data Rack - Dell PowerEdge HP ProLiant ThinkServer (4POSTRACK15U)

Product ID: 4POSTRACK15U



The 15U open frame rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 15U 4 post rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40 in.) that make it easy to adapt the adjustable server rack to fit your equipment.

This durable free standing server rack supports a static loading capacity of up to 1200 lb. (544 kg) and portable rolling weight capacity of 660 lb. (300 kg). The rack also features offers compliance with the EIA/ECA-310 standard for a universal design that's compatible with most network equipment rack equipment.

For a complete server storage solution that saves you time and hassle, the mobile server rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securely fastening the rack to the floor if needed, providing you with additional stability while free standing.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Suitable for rack-mount equipment where security at the rack level is not required
- Durable storage for rack-mount servers, KVM switches, and networking equipment
- Rack-mounting A/V equipment in a radio or television studio

Features

- **ADJUSTABLE DEPTH:** 15U Open frame rack with four vertical rails rack for servers & network equipment w/ adjustable mounting depth 23" to 41" (59cm to 104cm); maximize available space with 30" (77 cm) height, for integration in utility or server closet
- **EASY ASSEMBLY:** Mobile computer equipment rack with assembly instructions & easy-to-follow online video; compact flat pack shipping/packaging design to avoid damage and facilitate problem-free installations
- **COLD ROLLED STEEL:** Durable 4 Post 19" EIA/ECA-310-E open frame designed for ventilation with 15U mounting height, 1200lb (544lbs) capacity, 3 install options included: casters, levelling feet, or base-plate to secure rack to the floor
- **HARDWARE INCLUDED:** Rolling rack with cage nuts & screws to mount equipment, easy to read Units (U) & depth adjustment markings, cable management hooks for organization, with required assembly tools
- **STARTECH.COM ADVANTAGE:** Trusted by IT professionals for a variety of applications, this rack supports server depth equipment and can be used for servers, UPSs, patch panels, switches, and other networking or AV equipment. StarTech.com 2 Year Warranty and Free Lifetime Technical Support

Hardware

Warranty	2 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Open Frame
U Height	15U
Special Features	Adjustable Mounting Rails
	Base Plate with Floor-Anchoring Holes
	Built-in Cable Management
	Casters (Included)
	Grounding Lug(s)
	Leveling Feet

	Easy Assembly
	U-Markings
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity (Stationary)	1202.2 lb [544 kg]
------------------------------	--------------------

Physical Characteristics

Color	Black
Construction Material	Steel
Product Length	3.7 ft [1.1 m]
Product Width	23.6 in [60.0 cm]
Product Height	30.3 in [77.1 cm]
Weight of Product	60.6 lb [27.4 kg]
Maximum Mounting Depth	3.4 ft [1.0 m]
Minimum Mounting Depth	22.3 in [56.6 cm]
Product Height with Casters	33.2 in [84.4 cm]

Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	36.8 in [93.5 cm]
Package Width	10.8 in [27.5 cm]
Package Height	5.9 in [15.0 cm]
Shipping (Package) Weight	61.0 lb [27.6 kg]

**What's in the
Box**

Included in Package	
	Caster
	M6 Flange Nut
	M6 Flat Washer
	M6 Hex Screw
	Cable Management Hook
	Hook Mounting Screw
	Left Vertical Rail
	Right Vertical Rail
	Corner Section
	Center Section
	Top Bracket
	M8 Flat Washer
	M8 Hex Screw
	10mm Wrench
	13mm Wrench
	Philips Head Screwdriver
	Philips Head Screw
	Locking Washer
	M6 Screw
	M6 Plastic Washer
	M6 Cage Nut
	Leveling Feet
	Grounding Wire
	Manual

****Product appearance and specifications are subject to change without notice.***

