



DELL 24 MONITOR – E2420H

Elevate your everyday display.



ALL THE ESSENTIALS

Enhance your everyday workspace with a 1920 x 1080 resolution monitor with improved cable management and a smaller footprint.



DELL DISPLAY MANAGER

Superior productivity and manageability featuring quick access keys, preset layouts, multi-monitor configuration and remote management for IT managers.



AWARDED THE ENERGY STAR® MOST EFFICIENT MARK IN 2020¹

Delivering cutting edge energy-efficiency that represents the best in energy savings and environmental protection.¹



TRUSTED RELIABILITY

As the world's #1 monitor company*, we take pride in our unyielding commitment to quality and the utmost satisfaction of our customers.

Reliable, eco-friendly monitors at a great value



ALL THE ESSENTIALS

Screen performance: The 1920 X 1080 HD resolution is ideal for routine tasks, while ComfortView is ready for extended screen periods reducing up to 60% of harmful blue light emissions.²

Enhance your workspace: A thinner profile than the previous generation and improved cable management create a smaller footprint, lending itself to a clean, uncluttered desk.

Plug in: Quickly connect legacy or non-legacy PCs with VGA and DP ports.

Adapts to your needs: Make your workspace your own with VESA-compatible mounts and stands.



ECO-CONSCIOUS INSIDE AND OUT

Guaranteed green: With a comprehensive ENERGY STAR^{®1} certified portfolio, E series monitors meet stringent, energy requirements while in sleep, on and off modes. These monitors are also EPEAT registered, TCO-certified and meets all regulatory and environmental standards.

Reduce energy: Save energy with PowerNap³, a feature that dims or puts the monitor to sleep when not in use.

Clean disposal: Composting or recycling the packaging is easy since it's made with at least 75% recycled cardboard with zero Styrofoam packaging.⁴



DELL DISPLAY MANAGER

Productive at every level: Dell Display Manager's (DDM) Easy Arrange feature lets you quickly tile and view your applications side by side across one or more connected screens for multi-tasking efficiency.

Seamless transitions: The Auto-Restore feature remembers where you left off, so applications will go back to where you left them — even after you've unplugged.

The key to convenience: Shortcut keys can save you time, allowing quick access to commonly used controls that let you work faster.

More ways to manage: Asset management reports allow IT managers to quickly capture and track monitor information as well as configure multiple displays at once through a single setup.

THANK YOU FOR MAKING DELL MONITORS #1 WORLDWIDE**

Uncompromised testing: Rigorous development processes help ensure consistent, reliable performance in busy office environments.

Minimize downtime: Your monitor comes with a 3-year Advanced Exchange Service⁵ so that if a replacement becomes necessary, it will be shipped to you the next business day during your 3-year Limited Hardware Warranty.⁶

Get a higher level of support: Upgrade to 24 X 7, in-region technical phone support from qualified engineers with Dell ProSupport option.⁷

Features & Technical Specifications

Monitor	Dell 24 Monitor – E2420H
Diagonal Viewing Size	60.47 cm (23.8 inches)
Horizontal	527.04 mm (20.75 inches)
Vertical	296.46 mm (11.67 inches)
Maximum Preset Resolution	1920 x 1080 at 60 Hz
Aspect Ratio	16:9
Pixel Pitch	0.275 mm x 0.275 mm
Pixel Per Inch (PPI)	92
Brightness	250 cd/m ² (typical)
Color Support	Color gamut (typical): 83% (CIE1976) 72% (CIE1931) Color depth: 16.7 Million
Contrast Ratio	1000:1 (typical)
Viewing Angle	178°/178°
Response Time	8 ms typical (Normal) 5 ms typical (Fast) (gray to gray)
Panel Type	IPS (In-Plane Switching)
Display Screen Coating	Anti-Glare
Backlight Technology	LED
ComfortView with Flicker-free screen	Yes
Dell Display Manager Compatibility	Yes
Remote Asset Management	Yes, via Dell Command Monitor
GSA/TAA	No
Optional Soundbar	Dell Stereo Soundbar – AC511M
Connectivity	
Connectors	1 x VGA 1 x DisplayPort 1.2
HDCP Support	DisplayPort HDCP 1.2
Design Features	
Adjustability	Tilt Only (-5° to 21°)
Security	Security lock slot (cable lock sold separately)
Flat Panel Mount Interface	VESA (100 mm)
Power	
AC input voltage/frequency/current	100 VAC to 240 VAC / 50 Hz or 60 Hz ± 3 Hz / 0.8 A (typical)
Power Consumption (Operational)	5W (Typ). 22W (Max). 14.36W (ENERGY STAR®)
Power Consumption Stand by/Sleep	Less than 0.3W
Dimensions (with stand)	
Height	419.70 mm (16.52 inches)
Width	550.60 mm (21.68 inches)
Depth	171.0 mm (6.73 inches)
Weight	
Weight (panel only - for VESA mount/ no cables)	3.25 kg (7.17 lbs)
Weight (monitor and cables with stand)	4.27 kg (9.41 lbs)
Weight (with packaging)	5.95 kg (13.12 lbs)
Standard Service Plan	3-Years Advanced Exchange Service ⁵ and Limited Hardware Warranty ⁶
Optional Service Plan	Dell ProSupport ⁷
Environmental Compliance	Awarded the ENERGY STAR® Most Efficient Mark in 2020, EPEAT® registered where applicable ⁸ , TCO Certified Display

What's in the box?

Components

- Monitor with stand

Cables

- Power cable
- 1 x DP Cable (DP to DP)
- 1 x VGA Cable (EMEA and Japan only)
- 1 x VESA screw cover

Documentation

- Quick Setup Guide
- Safety and Regulatory Information

Recommended Accessories

DELL 24 MONITOR – E2420H

Easily adjust the panel to your preferred viewing position.



Back view -
Cable management slot



Tilt

Connectivity



- 1 Power connector
- 2 DisplayPort 1.2
- 3 VGA Port

RECOMMENDED ACCESSORIES



DELL SINGLE MONITOR ARM | MSA20

For greater viewing flexibility and a smaller footprint, choose the Dell Single Monitor Arm. Set up is virtually tool-free and its advanced cable management features offer a neat and clutter-free desk.



DELL STEREO SOUNDBAR | AC511M

The Dell Stereo Soundbar AC511M offers clear stereo sound, allowing you to enjoy audio on your favorite games, music and movies, without sacrificing desk space.



DELL WIRELESS KEYBOARD AND MOUSE | KM636

Designed with sleek lines, a compact size and chiclet keys, the Dell Wireless Keyboard and Mouse KM636 offers a contemporary and comfortable design with the convenience of wireless performance.

* Source: Based on publicly available share data, 2013 - Q2 2019.

** Dell monitors are #1 Worldwide for 6 consecutive years (2013-2019). Source: IDC Worldwide Quarterly PC Monitor Tracker, Q2 2019

1 This monitor is ENERGY STAR® certified and awarded the Energy Star Most Efficient Mark in 2020. For more information, visit <https://www.energystar.gov/most-efficient/most-efficient-computer-monitors>

2 Select Dell E, P and UltraSharp monitors feature flicker-free screens and ComfortView. Based on Dell internal analysis, August 2018. Actual blue light reduction will vary by model.

3 PowerNap is available via Dell Display Manager. Download the software at www.dell.com/ddm

4 Based on Dell internal analysis, Nov 2018. Excludes Dell D-series monitors.

5 Advanced Exchange Service: Dell will send you a replacement monitor the next business day in most cases, if deemed necessary after phone/online diagnosis. Shipping times may vary by location and for monitors 55" and above. Fee charged for failure to return defective unit. See dell.com/servicecontracts/global for details.

6 For a copy of the Limited Hardware Warranty, write to Dell USA LP, Attention: Warranties One Dell Way, Round Rock, TX 78682 or see dell.com/warranty for details.

7 Availability varies by region, please visit dell.com/support for details.

8 EPEAT registered where applicable. EPEAT registration varies by country. See www.epeat.net for registration status by country.

Dell.com/monitors Product availability varies by country. Please contact your Dell representative for more information.

© 2019 Dell. All rights reserved.

Trademarks or trade names may be used in this document to refer to either the entities claiming the marks and names of their products. Dell disclaims proprietary interest in the marks and names of others. Reproduction in any manner whatsoever without express written permission from Dell is strictly forbidden.

