

ThinkBook 14 IIL 20SL0015US

Product

ThinkBook 14 IIL

Region

NA

Country/Region

USA

Machine Type

20SL

TopSeller

TopSeller

Processor

Intel Core i5-1035G1 (4C / 8T, 1.0 / 3.6GHz, 6MB)

Graphics

Integrated Intel UHD Graphics

Chipset

Intel SoC Platform

Memory

8GB DIMM DDR4-2666

Storage

256GB SSD M.2 2242 PCIe NVMe 3.0x2

Display

14" FHD (1920x1080) IPS 250nits Anti-glare

Touchscreen

None

Optical

None

Media Reader

4-in-1 Card Reader

Ethernet

100/1000M

WLAN + Bluetooth

11ac, 2x2 + BT5.0

Case Material

Aluminium

Camera

720p with ThinkShutter

Microphone

2x, Array

Color

Mineral Grey

Keyboard

Backlit, English (US)

Fingerprint Reader

Touch Style

TPM

FW TPM 2.0

Battery

Integrated 45Wh

Power Adapter

65W Slim Tip

Operating System

Windows 10 Pro 64, English

Bundled Software

Office Trial

Base Warranty

1-year, Depot

Bundled Service

None

EAN / UPC / JAN

194632739206

End of Support

2025-12-25

Announce Date

2019-11-25

Recommended Services**Best**

3Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection) (5PS0N73156)

Better

3Y Lenovo Support (Premier Support + Keep Your Drive) (5PS0N73153)

Good

3Y Premier Support Upgrade from 1Y Depot/CCI (5WS0T36151)

Notes:**California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

L WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

ThinkBook 14 IIL Platform Specifications

Product Specifications Reference (PSREF)



Processor	10th Generation Intel® Core™ i3 / i5 / i7 Processor							Media reader Ports	4-in-1 media reader (MMC, SD, SDHC, SDXC) One hidden USB 2.0, two USB 3.1 Gen 1 (one Always On), One USB-C 3.1 Gen 1, one USB-C 3.1 Gen 2 (with the function of DisplayPort and power delivery), Ethernet (RJ45), HDMI 1.4b, 4-in-1 media reader (MMC, SD, SDHC, SDXC), headphone / microphone combo jack, AC power adapter jack <i>* Depending on many factors, actual data transfer speed may be lower than theoretical speed</i>	
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types			Processor Graphics
	i3-1005G1	2	4	1.2 GHz	3.4 GHz	4MB	DDR4-3200			Intel UHD Graphics
	i5-1035G1	4	8	1.0 GHz	3.6 GHz	6MB				Intel Iris® Plus Graphics
	i5-1035G4			1.1 GHz	3.7 GHz	6MB				
	i5-1035G7			1.2 GHz	3.7 GHz	6MB				
i7-1065G7	1.3 GHz			3.9 GHz	8MB					
Graphics	Intel UHD Graphics or Intel Iris Plus Graphics in processor only, or Intel UHD Graphics or Intel Iris Plus Graphics in processor and AMD Radeon™ 630, 2GB GDDR5 memory; supports external digital monitor via HDMI or USB Type-C; supports three independent displays; Max resolution: 3840x2160@60Hz (USB Type-C); 4096x2160@30Hz (HDMI)							Camera	HD720p camera with ThinkShutter, fixed focus, integrated dual array digital microphone	
Chipset	Intel SoC (System on Chip) platform							Audio support	HD Audio, Realtek ALC3287 codec, stereo speakers, 2W x 2, Dolby Audio™, dual array digital microphone	
Memory	16GB max / 2666MHz DDR4 or 3200MHz DDR4, one DDR4 SO-DIMM socket							Keyboard Trackpad	6-row, spill-resistant, multimedia Fn keys, optional LED backlight Buttonless Mylar surface touchpad, multi-touch	
Display	Size	Resolution	Surface	Type	Brightness	Aspect Ratio	Contrast Ratio	Security	Power-on password, hard disk password, supervisor password	
	14.0" (356mm)	FHD (1920x1080)	Anti-glare	TN	220 nits	16:9	500:1	Security chip	Firmware TPM 2.0 integrated in chipset	
	14.0" (356mm)	FHD (1920x1080)	Anti-glare	IPS	250 nits	16:9	800:1	Fingerprint reader	<i>Optional:</i> Touch style fingerprint reader on power button	
Multi-touch	None							Battery	Integrated Li-ion 45Wh (supports Rapid Charge 1 hr 80%) or 57Wh battery	
Storage	Up to 2 drives (one HDD and one M.2 SSD): • HDD / SATA 6.0Gb/s, 2.5" wide, 7mm high, Active Protection System • M.2 2242 SSD / PCIe NVMe, PCIe 3.0 x 2 • M.2 2280 SSD / PCIe NVMe, PCIe 3.0 x 4 • Intel Optane™ Memory H10 with SSD, M.2 2280, PCIe NVMe 3.0 x 4							Max battery life	<i>MobileMark® 2014:</i> 9 hr (45Wh) or 12 hr (57Wh) <i>* Battery life varies significantly with settings, usage, & other factors</i>	
Optical	None							AC adapter	65W slim tip (rectangle) or slim USB-C AC adapter	
Ethernet	Gigabit Ethernet connection							Preload (optional) <i>Preloaded operating system</i> • Windows® 10 Home 64 • Windows 10 Home in S mode • Windows 10 Pro 64 • Windows 10 Pro in S mode <i>Preloaded applications (only some listed)</i> • Microsoft Office 365 Personal • Microsoft Office 365 Home • Microsoft Office Home and Business 2019 • Microsoft Office Home and Student 2019 • Microsoft Office Trial (with 30-day license) • Microsoft Office Professional 2019 • Microsoft Office Personal 2019		
WLAN	One of the following, configurable by model: • 802.11ac 1x1 Wi-Fi + Bluetooth 5.0, M.2 card • 802.11ac 2x2 Wi-Fi + Bluetooth 5.0, M.2 card • 802.11ax 2x2 Wi-Fi + Bluetooth 5.0, M.2 card									
Bluetooth™	Bluetooth 5.0 wireless, integrated in Wi-Fi + Bluetooth combo adapter									
Dimensions	<i>WxDxH:</i> 12.8" x 9.06" x 0.7"; 326mm x 230mm x 17.9mm									
Weight	Starting at 3.3 lb / 1.5 kg									
Case color	Mineral Grey							Limited warranty	One of the following, configurable by model: • 1-year depot repair service • 1-year depot with 2-year system board repair service • 2-year/1-yr battery depot repair service	
Case material	Aluminum							Mil-Spec test	MIL-STD-810G military testing	
								Environment	EPEAT™ Silver; ENERGY STAR® 7.1; ErP lot3, RoHS-compliant	

Note: The specifications above may not be available in all regions.

Lenovo
February 2020

ThinkBook 14 IIL

