

Lenovo G27c-10 66A3GCCBUS

Product
Lenovo G27c-10

Machine Type
66A3

Region
NA,LA

Color
Raven Black

Panel
Vertical Alignment

Display Size
27"

View Area
597.89x336.31 mm

Resolution
1920x1080

Aspect Ratio
16:9

Pixel Pitch
0.3114x0.3114 mm

Dot / Pixel Per Inch
81.6 dpi

Brightness
350 nits

Contrast Ratio
3000:1

Pixel Response Time
4 ms (extreme mode) / 6 ms/14 ms (typical/off mode)

Color Gamut
72% NTSC

View Angle (H / V)
178 / 178

Stand
Tilt, Height Adjust Stand

Side Bezel Width
2.96 mm

Dimensions with Stand (HxWxD)
520.4x611.99x234.8 mm

Power Consumption (Typical / Maximum)
27W / 33W

Power Adapter
Integrated

Weight (Including Stand)
18.74 lb / 8.5 kg

Warranty
1-year

ENERGY STAR
None

TCO

None

EPEAT

None

Presets / User Settings

19

On Screen Display

OSD, 8 Languages

USB Port

None

Speaker

None

Camera

None

Low Blue Light / Eye Comfort

Low Blue Light & Flicker Free

Multiple Input

HDMI, DP

Monitor Cable

HDMI

End of Support

CPU / Platform

None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Operating System

Support Windows 7, Windows 10

Ann Date (mm/yy)

01/20



WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo G27c-10 Monitor

Lenovo

DISPLAY

Panel Size
27-inch

Screen Dimensions
597.89 mm x 336.31 mm

Panel Type
3-side NearEdgeless
VA

Curvature
1500R

Backlight
WLED

Aspect Ratio
16:9

Resolution
1920 x 1080

Pixel Pitch
0.3114 x 0.3114 mm

Dot/Pixel Per Inch (DPI/PPI)
81.6

Viewing Angle (H x V @ CR 10:1)
178° / 178°

Response Time
4ms (extreme mode)

Refresh Rate
165 Hz

Brightness (typical)
350 cd/m²

Contrast Ratio (typical)
3000:1

Dynamic Contrast Ratio (typical)
3M:1

Color Gamut
72%

Color Support (typical)
16.7 Million

Anti-glare
Yes

CONNECTIVITY

Video Signal
1 x HDMI 2.0
1 x DP 1.2

Audio Signal
1 x Audio Out (3.5 mm)

SPECIAL FEATURES

Sync Technology
AMD Radeon FreeSync™*

POWER

Power Consumption (typical/max)
33W / 27W

Power Consumption Sleep/Off Mode
< 0.5W

Power Consumption Switch-off Mode
< 0.3W

Voltage Required
AC 90 to 264 V (47/63 Hz)

MECHANICAL

Tilt Angle (front/back)
-5° / 22°

Lift (max range)
130 mm

VESA Mount Capability
Yes (100 x 100 mm)

Kensington Lock Slot
Yes

Cable Management
Yes

Bezel Color
Raven Black

Bezel Width (side)
2.96 mm

Bezel Width (top/bottom)
2.96 / 15.16 mm

DIMENSION

Size Packed (D x H x W, mm/inch)
250 x 472 x 724 mm /
9.84 x 18.58 x 28.5 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (lowest position)
234.8 x 390.4 x 611.99 mm /
9.24 x 19.31 x 24.09 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (highest position)
234.80 x 520.4 x 611.99 mm /
9.24 x 20.49 x 24.09 inches

Weight Packed (kg/lbs.)
8.5 kg / 18.74 lbs.

Weight Unpacked (kg/lbs.)
6.1 kg / 13.45 lbs.

WHAT'S IN THE BOX

Monitor with stand
Information flyer
1 x HDMI cable (1.8 m)
1 x Power cable (1.8 m)

CERTIFICATION

CCC
Yes

RoHS (EU 2002/95/EC)
Yes

Windows Certification
Windows 7, Windows 10

China Energy Efficiency Standard
Tier 1

TÜV Rheinland Low Blue Light /
TÜV Rheinland Flicker Free
Yes



*AMD Radeon FreeSync™ can only work with AMD Radeon™ series graphics card

Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: - 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2020 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

Lenovo G27c-10

Lenovo

