

Lenovo G34w-10 66A1GCCBUS

Product

Lenovo G34w-10

Machine Type

66A1

Region

LA,NA

Display Size

34"

View Area

797.22x333.72 mm

Panel

Vertical Alignment

Aspect Ratio

21:9

Resolution

3440x1440

Pixel Pitch

0.232x0.232 mm

Dot / Pixel Per Inch

109 dpi

View Angle (H / V)

178 / 178

Pixel Response Time

4 ms (Extreme mode) / 6 ms (Typical mode) / 14 ms (off mode)

Brightness

350 nits

Contrast Ratio

3000:1

Color Gamut

72% NTSC

Multiple Input

HDMI, DP

USB Port

None

Camera

None

Speaker

None

Power Consumption (Typical / Maximum)

43W / 50W

Power Adapter

Integrated

Stand

Tilt, Height Adjust Stand

Color

Black

Side Bezel Width

1.9 mm

Dimensions with Stand (HxWxD)

541.84x808.6x259.96 mm

Weight (Including Stand)

17.85lb / 8.1kg

Monitor Cable

DP

ENERGY STAR

None

TCO

None

EPEAT

None

Low Blue Light / Eye Comfort

Low Blue Light & Flicker Free

Base Warranty

1-year

Operating System

Support Windows 7, Windows 10

Presets / User Settings

27 / 27

On Screen Display

OSD, 8 Languages

CPU / Platform

None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Ann Date (mm/yy)

01/20



WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



Specifications

DISPLAY

Panel Size

34-inch

Screen Dimensions

797.22 mm x 333.72 mm

Panel Type

3-side NearEdgeless
VA

Curvature

1500R

Backlight

WLED

Aspect Ratio

21:9

Resolution

3440 x 1440

Pixel pitch

0.232 x 0.232 mm

Dot/Pixel Per Inch (DPI/PPI)

109

Viewing Angle (H x V @ CR 10:1)

178° / 178°

Response Time

4ms (extreme mode)

Refresh Rate

144 Hz

Brightness (typical)

350 cd/m²

Contrast Ratio (typical)

3000:1

Dynamic Contrast Ratio

3M:1

Color Gamut

72% NTSC

Color Support (typical)

16.7 Million

Anti-glare

Yes

CONNECTIVITY

Video Signal

1 x HDMI 2.0
1 x DP 1.4

Audio Signal

1 x Audio Out (3.5 mm)

SPECIAL FEATURES

Sync Technology

AMD Radeon FreeSync™

POWER

Power Consumption (typ./max)

43W / 50W

Power Consumption Sleep/Off Mode

< 0.5W

Power Consumption Switch-off Mode

< 0.3W

MECHANICAL

Tilt Angle (front/back)

-5° / 22°

Lift (max range)

130 mm

VESA Mount Capability

Yes (100 x 100 mm)

Kensington Lock Slot

Yes

Cable Management

Yes

Bezel Color

Black

Bezel Width (side)

1.9 mm

Bezel Width (top/bottom)

1.9 / 17.8 mm

DIMENSION

Size Packed (D x H x W, mm/inch)

281 x 489 x 943mm /
11.06 x 19.25 x 37.12 inches

Size Unpacked w/stand (D x H x W, mm/inch) (lowest position)

259.96 x 411.84 x 808.6 mm /
10.23 x 16.21 x 31.81 inches

Size Unpacked w/stand (D x H x W, mm/inch) (highest position)

259.96 x 541.84 x 808.6 mm /
10.23 x 21.33 x 31.81 inches

Weight Packed (kg/lbs.)

11.3 kg / 24.91 lbs.

Weight Unpacked (kg/lbs.)

8.1 kg / 17.85 lbs.

WHAT'S IN THE BOX

Monitor with stand

1 x Power cable

1 x DP cable (1.8 m)

Quick setup guide

CERTIFICATION

TÜV Rheinland Low Blue Light /

TÜV Rheinland Flicker Free

Yes



*AMD Radeon FreeSync™ can only work with AMD Radeon™ graphics card

© 2020 Lenovo. All rights reserved. Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: - 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Lenovo G34w-10

Lenovo™

