

# Lenovo 300e Chromebook 2nd Gen 81MB001DUS

**Product**  
Lenovo 300e Chromebook 2nd Gen

**Region**  
NA

**Country/Region**  
USA

**Machine Type**  
81MB

**TopSeller**  
TopSeller

**Processor**  
Intel Celeron N4020 (2C / 2T, 1.1 / 2.8GHz, 4MB)

**Graphics**  
Integrated Intel UHD Graphics 600

**Chipset**  
Intel SoC Platform

**Memory**  
4GB Soldered LPDDR4-2400

**Storage**  
32GB eMMC 5.1

**Display**  
11.6" HD (1366x768) IPS 250nits Anti-glare

**Touchscreen**  
10-point Multi-touch

**Optical**  
None

**Media Reader**  
MicroSD Card Reader

**Ethernet**  
None

**WLAN + Bluetooth**  
Intel 9560 11ac, 2x2 + BT4.2

**Case Material**  
PC / ABS

**Camera**  
720p + World Facing 5.0MP

**Microphone**  
Mono

**Color**  
Black

**Keyboard**  
Non-backlit, English

**Fingerprint Reader**  
None

**TPM**  
Google Security Chip H1

**Battery**  
Integrated 42Wh

**Power Adapter**  
45W USB-C

**Operating System**  
Chrome OS

**Bundled Software**  
None

**Base Warranty**  
1-year, Mail-in

**Bundled Service**  
None

**EAN / UPC / JAN**  
194632384567

**End of Support**  
2026-01-09

**Announce Date**  
2019-12-09

## Notes:

### California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

 [WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.  
© Lenovo, 2020. All rights reserved.



## Lenovo 300e Chromebook 2<sup>nd</sup> Gen Platform Specifications

Product Specifications Reference (PSREF)

Processor	Intel® Celeron® Processor								4MB	LPDDR4 2400	Intel UHD Graphics 600	Camera	720p HD, fixed focus, single microphone, optional 5MP World Facing camera, single microphone			
												Audio support	Maxim MAX98357A Dialog DA7219, stereo speakers, 2W x 2, single microphone, headphone / microphone combo jack			
												Keyboard Touchpad	6-row, Anti-pry Key Caps, spill-resistant One-piece touchpad			
												Security	Security keyhole			
Graphics	Intel UHD Graphics 600 in processor											Security chip	Google security chip H1			
Chipset	Intel SoC (System on Chip) platform											Fingerprint reader	None			
Memory	4GB or 8GB/ 2400MHz LPDDR4 / soldered to systemboard											Battery type	Integrated Li-ion 42Wh battery			
Display	11.6" (295mm) HD (1366x768), IPS, anti-glare, anti-fingerprint, LED backlight, 250 nits, 16:9 aspect ratio											Max battery life	Up to 10hrs <small>* Battery life varies significantly with settings, usage, &amp; other factors.</small>			
Multi-touch	Enhanced Touch, anti-fingerprint, support 10-finger gesture											AC adapter	45W USB Type-C AC adapter			
Storage	32GB eMMC 5.1 (embedded Multi Media Card) flash memory on board											Preload	Google Chrome OS			
Optical	None											Limited warranty	<i>One of the following, configurable by model:</i> <ul style="list-style-type: none"><li>• 1-year mail-in repair service</li><li>• 1-year depot repair service</li><li>• 2-year/1-yr battery depot repair service</li></ul>			
Ethernet	None											Mil-Spec test	MIL-STD-810G military testing			
WLAN	Intel 9560, Wi-Fi 2x2 802.11ac + Bluetooth 4.2, M.2 card											Environment	EPEAT™ Silver; RoHS-compliant			
Bluetooth™	Bluetooth 4.2 wireless, integrated in Wi-Fi + Bluetooth combo adapter															
WWAN	None															
Dimensions	WxDxH: 11.42" x 8.03" x 0.80"; 290mm x 204mm x 20.35mm															
Weight	1.31 kg (2.9 lb)															
Case color	Black															
Case material	PC/ABS plastic															
Media reader	MicroSD card reader															
Ports	Two USB-C 3.1 Gen 1 (with the function of power delivery, DisplayPort and data transfer), two USB-A 3.1 Gen 1, headphone / microphone combo jack, MicroSD card reader, security keyhole															
<small>* Depending on many factors, actual data transfer speed may be lower than theoretical speed.</small>																

Note: The specifications above may not be available in all regions.

Lenovo  
January 2020

# Lenovo 300e Chromebook 2nd Gen

Lenovo



G Suite for Education

