

## OVERVIEW

Basic rPDUs deliver reliable power to critical IT equipment within a rack or cabinet.

### Benefits

- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



## Part #: 11405VH

**Model Number:** NSVLN080-101S15

**Category:** Basic

**Sub Category:** Standard

**Power Configuration:** 15A, 120V, 1.4kW

**Physical Configuration:** 17in / 432mm, Horizontal/Vertical

**Product Summary:** 11405 - rPDU, Basic Standard, 15A, 120V, 1.4kW, Horizontal/Vertical, (8) NEMA 5-15R, 10ft power cord with 5-15P, Black Powder Coat.

### Plug Form:



5-15P

### Receptacle:



NEMA 5-15R  
(Quantity: 8)

### Chassis Color Options:



To discuss color options, contact your local sales representative.

## Product Specification and Options

### System Features

Quantity Of Inputs	1
Voltage	100-120V
Current	15A
VA per Input (Load Capacity)	1.4kW (120V)

<b>Frequency</b>	50/60Hz
<b>Over Current Protection</b>	15A Thermal Breaker
<b>Switch</b>	No
<b>Indicators - LED(s)</b>	1 - Power ON Green LED
<b>Power Cable Wire Gauge</b>	14/3
<b>Power Cable Length</b>	10ft
<b>Plug Type</b>	NEMA 5-15P
<b>Receptacle/Socket Type #1</b>	NEMA 5-15R
<b>- Quantity on Face</b>	8
<b>- Quantity per Breaker</b>	8
<b>- Style</b>	Individual - In-Line
<b>- Maximum Output per Receptacle/Socket</b>	15A
<b>- Voltage per Receptacle/Socket</b>	120V
<b>Center to Center Receptacle Spacing</b>	1.25
<b>Continuous Operating Temperature Range</b>	10-45C / 50-113F
<b>Heavy Steel - Powder Coat Finish</b>	Black
<b>Configuration</b>	17in / 432mm Vertical/Horizontal Rackmount
<b>19in Panel Mount Brackets</b>	Yes
<b>Plastic Mounting Clips</b>	1 - Bottom; 1 - Top
<b>Country of Origin</b>	USA, TAA Compliant
<b>Product Warranty</b>	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
<b>Certification/Agency Approvals</b>	RoHS Compliant
<b>Certification/Agency Approvals</b>	UL & c-UL Listed 60950
<b>Chassis Dimensions (LxWxD)</b>	17.00in x 1.61in x 1.61in
<b>Shipped Weight</b>	4lbs (1.81kg)