

15U 19" Server Rack Cabinet - 4 Post Adjustable Depth (6-32") Locking Knock Down Network/Computer Equipment Enclosure - Mobile w/Glass Door & Casters - HP ProLiant ThinkServer

Product ID: RK1536BKF



This 15U server rack cabinet provides plenty of storage space in a sleek secure cabinet for storing EIA-310 compliant 19 inch rackmount devices such as Dell, HP and IBM servers along with telecommunication, A/V and IT equipment.

Hassle-Free Equipment Installation

This knock down server rack has been engineered with different features that enable you to easily incorporate plenty of equipment. With adjustable mounting rails you can easily change the rail depth to up to 32 in. (813 mm).

Securely Protect Your Equipment

To ensure you have full visibility of your equipment while securely locking it up, this rack has a stylish glass window on the front door. The server rack with glass door also has removable side panels with independent lock with quick-release mechanisms that enable you to easily access your network equipment.

Maximum Maneuverability

The server rack with wheels ensures hassle-free access to the rear mounted equipment, while providing ease of mobility around your office or server room. Once the network equipment enclosure is at the intended location you can stabilize it using the built-in leveling feet in floor standing applications.

The Choice of IT Pros Since 1985

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

The RK1536BKF is backed by a lifetime StarTech.com warranty with free technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for rack-mount servers, KVM switches, networking equipment and cabinet consoles
- Perfect solution for technology shops and repair centers with limited space and mountable equipment where security is required
- Audio/Video editing room, radio or television studio broadcast rack-mount equipment Audio/Video editing room, radio or television studio broadcast rack-mount equipment

Features

- 15U 4-POST CABINET: Server rack cabinet features all metal 4 post design with 15U, adjustable depth, casters & levelling feet, removable locking sides/doors & top/bottom/front/rear cable access
- STRAIGHT FORWARD ASSEMBLY: Knock down network data equipment enclosure comes in an easy ship flat pack, with clear assembly instructions & supporting videos; includes tools needed for assembly
- SERVER READY: EIA/ECA 310-E standard server rack cabinet with internal depth of 39" and an adjustable mounting depth of 6-32" in a compact 39" tall design
- MOBILITY & STABILITY: Mobile computer rack features a 1768 lb capacity, solid metal floor which can be used as a shelf, casters & levelling feet & rear and top mesh w/ vented lockable glass front door
- THE STARTECH.COM ADVANTAGE: StarTech.com offers a lifetime warranty and free lifetime technical support on this cabinet, and has been the choice of IT professionals and businesses for over 30 years

Hardware	Warranty	Lifetime
	Frame Type	Enclosed Cabinet
	Front Door Construction	Steel with Glass Window
	Front Door Features	Secure Key Lock with Reversible and Removable Front Door
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	G-Shape
	Rack Type	4-Post
	Rear Door Construction	Steel Mesh
	Rear Door Features	Secure Key Lock with Reversible and Removable Back Door
	Side Panel Construction	Steel
	Side Panel Features	Secure Key Lock with Removable Side Panels
	Special Features	Casters (Included)
		Easy Assembly
		Grounding Lug(s)
	Leveling Feet	
	U-Markings	
	Adjustable Mounting Rails	
	U Height	15U
	Wallmountable	No
Performance	Weight Capacity (Stationary)	1768 lb [800 kg]
Physical Characteristics	Color	Black
	Construction Material	Steel
Product Measurements	Internal Depth	39.1 in [99.2 cm]
	Internal Width	23.5 in [59.6 cm]
	Maximum Mounting Depth	32 in [81.3 cm]
	Minimum Mounting Depth	5.5 in [14 cm]
	Product Height	31.4 in [79.6 cm]
	Product Height with Casters	33.9 in [86.1 cm]
	Product Length	39.4 in [100 cm]

	Product Width	23.6 in [60 cm]
	Weight of Product	128.2 lb [58 kg]
Packaging Information	Flat Pack (Assembly Required)	Yes
	Package Height	12.9 in [32.7 cm]
	Package Length	42 in [106.7 cm]
	Package Width	34.4 in [87.3 cm]
	Shipping (Package) Weight	138.3 lb [62.6 kg]
What's in the Box	Included in Package	<ul style="list-style-type: none"> 2 - Side Panel and Frame 4 - Upper and Lower Beams 1 - Top Panel 2 - Bottom Panel with Cable Management Slot 1 - Bottom Panel (Solid) 1 - Front Door 1 - Rear Door 8 - Plastic Corner Caps 8 - M8-20 Hex Screw 8 - M8 Spring Washer 8 - M4-10 Flat Head Screw 4 - M6-12 Hex Screw 6 - M5-12 Screw 1 - M6 Hex Key 1 - M8 Hex Key 24 - M6-12 Philips Screws 24 - M6 Cage Nuts 24 - M6 Plastic Cup Washers 2 - Caster 2 - Caster with Brake 16 - M6-10 Philips Bolt 4 - Leveling Feet 2 - Door Key 2 - Side Panel Key

2 - Door Hinge Pin

1 - Philips Screwdriver

Product appearance and specifications are subject to change without notice.