

OVERVIEW

Basic rPDUs deliver reliable power to critical IT equipment within a rack or cabinet.

Benefits

- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



Part #: 11112VH

Model Number: 2XPR060-103L20TL6

Category: Basic

Sub Category: Standard

Power Configuration: 30A, 208V, 4.9kW

Physical Configuration: 2U 19in / 483mm, Horizontal

Product Summary:

rPDU, Basic Standard, 30A, 208V, 4.9kW, Horizontal, (6) NEMA L6-20R, 10ft power cord with L6-30P, Black Powder Coat.

Plug Form:



L6-30P

Receptacle:



NEMA L6-20R
(Quantity: 6)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Quantity Of Inputs	1
Voltage	200-240V
Current	30A
VA per Input (Load Capacity)	4.9kW (208V)
Frequency	50/60Hz
Over Current Protection	(2) 20A Double Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	10/3
Power Cable Length	10ft
Plug Type	NEMA L6-30P Twistlock
Receptacle/Socket Type #1	NEMA L6-20R
- Quantity on Rear	6
- Quantity per Breaker	3
- Style	Individual
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	208V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	19in / 483mm Horizontal Rackmount
19in Recess Mount	Yes
Country of Origin	USA, TAA Compliant
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	3.39in x 17in x 6in
Shipped Weight	15lbs (6.8kg)