

OVERVIEW

Basic rPDUs deliver reliable power to critical IT equipment within a rack or cabinet.

Benefits

- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



Part #: 11856VH

Model Number: VHVBN302-102IN6TL6

Category: Basic

Sub Category: Standard

Power Configuration: 20A, 208V, 3.3kW

Physical Configuration: 66in / 1683mm, Vertical

Product Summary: rPDU, Basic Standard, 20A, 208V, 3.3kW, Vertical, (24) IEC C13, (6) IEC C19, 10ft power cord with L6-20P, Black Powder Coat.

Plug Form:



L6-20P

Receptacle:



IEC C13
(Quantity: 24)



IEC C19
(Quantity: 6)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Quantity Of Inputs	1
Voltage	200-240V
Current	20A
VA per Input (Load Capacity)	3.3kW (208V)
Frequency	50/60Hz

Over Current Protection	None
Switch	No
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA L6-20P Twistlock
Combined Total Receptacle/Socket Quantity	30
Receptacle/Socket Type #1	IEC C13
- Quantity on Face	24
- Style	Banks of 4
- Maximum Output per Receptacle/Socket	15A per receptacle bank
- Voltage per Receptacle/Socket	208V
Receptacle/Socket Type #2	IEC C19
- Quantity on Face	6
- Style	Individual
- Maximum Output per Receptacle/Socket	20A
- Voltage per Receptacle/Socket	208V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	66in / 1683mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Country of Origin	USA, TAA Compliant
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 2.0in x 2.0in
Shipped Weight	15lbs (6.8kg)