

## OVERVIEW

Basic rPDUs deliver reliable power to critical IT equipment within a rack or cabinet.

### Benefits

- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



## Part #: U1077

**Model Number:** DU00X2R1-24CF17-2S02A9H00-S

**Category:** Basic

**Sub Category:** Standard

**Power Configuration:** Variable, Max 22.0kW

**Physical Configuration:** 19in / 483mm, Horizontal

**Product Summary:** rPDU, Basic Standard, Max 22.0kW, Variable Power Configuration, Horizontal, (24) Combination C13/C19, Universal Input, Black Powder Coat.

### Plug Form:



Universal Input

### Receptacle:



Combination C13/C19  
(Quantity: 24)

### Chassis Color Options:



To discuss color options, contact your local sales representative.

## Product Specification and Options

### System Features

Quantity Of Inputs	1
Maximum Input Power (Defined by Facility Side Cable)	63A Single Phase, 240V Max, 14.4kW 48A 3 Phase DELTA, 240V Max, 19.9kW 32A Three Phase WYE, 240/415V Max, 22.0kW
Frequency	50/60Hz
Over Current Protection	(6) 16A Double Pole Magnetic Breakers (10kAIC Rated)

<b>Switch</b>	<b>Breaker/Switch Combination</b>
<b>Power Entry Location</b>	Left Rear
<b>Plug Type</b>	Universal Inlet
<b>Receptacle/Socket Type #1</b>	Combination C13/C19
<b>- Quantity on Rear</b>	24
<b>- Quantity per Breaker</b>	4
<b>- Circuit Color ID</b>	6 Circuit = Orange, Light Orange, Green, Light Green, Blue, Light Blue
<b>- Style</b>	Banks of 6
<b>- Voltage per Receptacle/Socket</b>	Defined by Facility Side Cable
<b>Maximum Operating Temperature</b>	60C / 140F
<b>Heavy Steel - Powder Coat Finish</b>	Black
<b>Configuration</b>	2U
<b>19in Recess Mount</b>	Yes
<b>Product Warranty</b>	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
<b>Certification/Agency Approvals</b>	CE Marked
<b>Certification/Agency Approvals</b>	RoHS Compliant
<b>Certification/Agency Approvals</b>	UL Listed 60950
<b>Chassis Dimensions (HxWxD)</b>	3.39in x 17in x 9in / 87mm x 432mm x 229mm
<b>Shipped Weight</b>	16lbs (7.26kg)